

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284023

Luminaire Tested: P3AS09R65B2750DE010 E3CD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65B2750DE010 E3CD1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 713.1 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284023

CATALOG NUMBER: P3AS09R65B2750DE010 E3CD1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284023

CATALOG NUMBER: P3AS09R65B2750DE010 E3CD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174240
5°	163988
10°	161899
15°	159047
20°	150163
25°	139387
30°	108346
35°	62667
40°	25247
45°	11629
50°	4537
55°	1759
60°	1535
65°	1505
70°	1475
75°	1440
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 11629 cd/sqm

TEST NUMBER: P1284023

CATALOG NUMBER: P3AS09R65B2750DE010 E3CD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.8	9.9
10°-20°	195.6	27.4
20°-30°	256.1	35.9
30°-40°	148.4	20.8
40°-50°	31.8	4.5
50°-60°	5.2	0.7
60°-70°	2.9	0.4
70°-80°	1.7	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	522.6	73.3
0°-40°	670.9	94.1
0°-60°	707.9	99.3
0°-90°	713.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	713.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	795	
5°	745	71
15°	701	196
25°	576	256
35°	234	148
45°	38	32
55°	5	5
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1284023

CATALOG NUMBER: P3AS09R65B2750DE010 E3CD1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	794.6
2.5°	772.1
5°	745.0
7.5°	734.1
10°	727.1
12.5°	717.3
15°	700.6
17.5°	674.7
20°	643.5
22.5°	614.1
25°	576.1
27.5°	512.1
30°	427.9
32.5°	331.6
35°	234.1
37.5°	148.2
40°	88.2
42.5°	55.4
45°	37.5
47.5°	24.2
50°	13.3
52.5°	6.3
55°	4.6
57.5°	4.0
60°	3.5
62.5°	3.5
65°	2.9
67.5°	2.3
70°	2.3
72.5°	1.7
75°	1.7
77.5°	1.2
80°	1.2
82.5°	0.6
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)