

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284045

Luminaire Tested: P3AS09R65B2750DE010 E3D1WH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65B2750DE010 E3D1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 80CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 700.0 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284045
CATALOG NUMBER: P3AS09R65B2750DE010 E3D1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284045
 CATALOG NUMBER: P3AS09R65B2750DE010 E3D1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77				77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67				67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63				63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59				59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187573
5°	174158
10°	168423
15°	162316
20°	150046
25°	136726
30°	105637
35°	61221
40°	24303
45°	10358
50°	2456
55°	344
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10358 cd/sqm



TEST NUMBER: P1284045
 CATALOG NUMBER: P3AS09R65B2750DE010 E3D1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	10.7
10°-20°	199.2	28.5
20°-30°	252.1	36.0
30°-40°	143.6	20.5
40°-50°	28.6	4.1
50°-60°	1.5	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	526.0	75.1
0°-40°	669.6	95.6
0°-60°	699.6	99.9
0°-90°	700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	855	
5°	791	75
15°	715	199
25°	565	252
35°	229	144
45°	33	29
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1284045
CATALOG NUMBER: P3AS09R65B2750DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	855.4
1°	849.1
2°	835.2
3°	819.1
4°	803.3
5°	791.2
6°	782.3
7°	775.1
8°	768.8
9°	762.5
10°	756.4
11°	749.8
12°	742.9
13°	734.5
14°	725.6
15°	715.0
16°	702.3
17°	688.5
18°	673.5
19°	657.7
20°	643.0
21°	628.1
22°	614.6
23°	600.5
24°	584.1
25°	565.1
26°	542.3
27°	515.0
28°	484.2
29°	451.4
30°	417.2
31°	379.5
32°	342.1
32.5°	322.8
33°	304.1
34°	266.1
35°	228.7
36°	194.2
37°	160.0
37.5°	142.4
38°	128.3
39°	103.9
40°	84.9
42.5°	52.4
45°	33.4



TEST NUMBER: P1284045
CATALOG NUMBER: P3AS09R65B2750DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	19.6
50°	7.2
52.5°	1.4
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)