

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284081

Luminaire Tested: P3AS09R65B2750DE010 E3DL1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284081
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65B2750DE010 E3DL1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 80CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 628.0 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284081

CATALOG NUMBER: P3AS09R65B2750DE010 E3DL1WMH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284081

CATALOG NUMBER: P3AS09R65B2750DE010 E3DL1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148102
5°	146335
10°	140768
15°	131874
20°	118614
25°	100724
30°	78772
35°	56135
40°	36726
45°	22700
50°	11531
55°	4052
60°	3552
65°	3580
70°	3206
75°	3219
80°	3157
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22700 cd/sqm

TEST NUMBER: P1284081

CATALOG NUMBER: P3AS09R65B2750DE010 E3DL1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	9.9
10°-20°	161.7	25.7
20°-30°	188.9	30.1
30°-40°	132.0	21.0
40°-50°	58.1	9.3
50°-60°	12.9	2.1
60°-70°	6.6	1.0
70°-80°	4.0	0.6
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.0	65.8
0°-40°	545.0	86.8
0°-60°	616.1	98.1
0°-90°	628.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	628.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	675	
5°	665	62
15°	581	162
25°	416	189
35°	210	132
45°	73	58
55°	11	13
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1284081

CATALOG NUMBER: P3AS09R65B2750DE010 E3DL1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	675.4
2.5°	672.9
5°	664.8
7.5°	651.0
10°	632.2
12.5°	609.0
15°	580.9
17.5°	546.4
20°	508.3
22.5°	465.1
25°	416.3
27.5°	364.9
30°	311.1
32.5°	259.1
35°	209.7
37.5°	166.5
40°	128.3
42.5°	97.0
45°	73.2
47.5°	53.8
50°	33.8
52.5°	17.5
55°	10.6
57.5°	9.4
60°	8.1
62.5°	7.5
65°	6.9
67.5°	5.6
70°	5.0
72.5°	4.4
75°	3.8
77.5°	3.1
80°	2.5
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)