

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283157

Luminaire Tested: P3AS09R35B2750DE010 E3CB1MMS_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283157
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35B2750DE010 E3CB1MMS_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 743.0 lumens
Efficiency: N/A
Efficacy: 56.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283157

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1283157

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93			
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89			
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86			
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83			
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80			
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	77			
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75			
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73			
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	484479
5°	474619
10°	441542
15°	323702
20°	165751
25°	59737
30°	23269
35°	8138
40°	3349
45°	899
50°	785
55°	879
60°	789
65°	623
70°	769
75°	1017
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 1017 cd/sqm

TEST NUMBER: P1283157

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.0	27.1
10°-20°	377.1	50.8
20°-30°	133.5	18.0
30°-40°	23.4	3.1
40°-50°	3.4	0.5
50°-60°	1.9	0.3
60°-70°	1.4	0.2
70°-80°	1.0	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.7	95.8
0°-40°	735.1	98.9
0°-60°	740.4	99.6
0°-90°	743.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	743.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2209	
5°	2156	201
15°	1426	377
25°	247	134
35°	30	23
45°	3	3
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1283157

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2209.4
1°	2208.8
2°	2201.8
3°	2188.4
4°	2176.1
5°	2156.2
6°	2135.7
7°	2112.9
8°	2084.8
9°	2040.9
10°	1983.0
11°	1902.8
12°	1806.3
13°	1691.6
14°	1565.2
15°	1425.9
17.5°	1062.0
20°	710.3
22.5°	428.3
25°	246.9
27.5°	147.5
30°	91.9
32.5°	53.2
35°	30.4
37.5°	19.3
40°	11.7
42.5°	5.9
45°	2.9
47.5°	2.3
50°	2.3
52.5°	2.3
55°	2.3
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0



TEST NUMBER: P1283157

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)