

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283161

Luminaire Tested: P3AS09R35B2750DE010 E3CB1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283161
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35B2750DE010 E3CB1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 80CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 796.0 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283161

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283161

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93			
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89			
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86			
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83			
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80			
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	77			
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75			
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73			
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	519037
5°	508473
10°	473026
15°	346812
20°	177582
25°	63996
30°	24915
35°	8727
40°	3578
45°	961
50°	853
55°	956
60°	833
65°	675
70°	833
75°	1101
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 1101 cd/sqm

TEST NUMBER: P1283161

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.3	27.1
10°-20°	404.1	50.8
20°-30°	143.1	18.0
30°-40°	25.0	3.1
40°-50°	3.7	0.5
50°-60°	2.0	0.3
60°-70°	1.5	0.2
70°-80°	1.1	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.5	95.8
0°-40°	787.5	98.9
0°-60°	793.2	99.6
0°-90°	796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2367	
5°	2310	215
15°	1528	404
25°	264	143
35°	33	25
45°	3	4
55°	2	2
65°	1	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1283161

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2367.0
1°	2366.4
2°	2358.9
3°	2344.5
4°	2331.3
5°	2310.0
6°	2288.0
7°	2263.6
8°	2233.5
9°	2186.5
10°	2124.4
11°	2038.6
12°	1935.1
13°	1812.3
14°	1676.9
15°	1527.7
17.5°	1137.8
20°	761.0
22.5°	458.9
25°	264.5
27.5°	158.0
30°	98.4
32.5°	57.0
35°	32.6
37.5°	20.7
40°	12.5
42.5°	6.3
45°	3.1
47.5°	2.5
50°	2.5
52.5°	2.5
55°	2.5
57.5°	1.9
60°	1.9
62.5°	1.9
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0



TEST NUMBER: P1283161

CATALOG NUMBER: P3AS09R35B2750DE010 E3CB1MMS_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)