

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283188

Luminaire Tested: P3AS09R35B2750DE010 E3DL1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1283188  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R35B2750DE010 E3DL1GPH\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 297.0 lumens  
Efficiency: N/A  
Efficacy: 22.7 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1283188  
CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1GPH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1283188  
 CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	69	76	71	68	75	71	68	74	70	68	67	67	67	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	149791
5°	143957
10°	125426
15°	96073
20°	64266
25°	38881
30°	22307
35°	12474
40°	6641
45°	3411
50°	1637
55°	1300
60°	1228
65°	1038
70°	1090
75°	932
80°	1010
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3411 cd/sqm



TEST NUMBER: P1283188

CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.5	20.0
10°-20°	115.3	38.8
20°-30°	75.5	25.4
30°-40°	30.6	10.3
40°-50°	9.2	3.1
50°-60°	3.1	1.1
60°-70°	2.1	0.7
70°-80°	1.2	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.3	84.3
0°-40°	280.9	94.6
0°-60°	293.2	98.7
0°-90°	297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	683	
5°	654	60
15°	423	115
25°	161	75
35°	47	31
45°	11	9
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1283188  
CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	683.1
1°	682.0
2°	678.9
3°	672.7
4°	665.3
5°	654.0
6°	639.9
7°	624.1
8°	606.3
9°	585.9
10°	563.3
11°	538.2
12°	511.9
13°	482.5
14°	454.6
15°	423.2
17.5°	347.2
20°	275.4
22.5°	211.9
25°	160.7
27.5°	119.8
30°	88.1
32.5°	64.7
35°	46.6
37.5°	33.1
40°	23.2
42.5°	16.1
45°	11.0
47.5°	7.3
50°	4.8
52.5°	3.7
55°	3.4
57.5°	3.1
60°	2.8
62.5°	2.5
65°	2.0
67.5°	1.7
70°	1.7
72.5°	1.4
75°	1.1
77.5°	0.8
80°	0.8
82.5°	0.6
85°	0.3
87.5°	0.3



TEST NUMBER: P1283188  
CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1GPH\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)