

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283213

Luminaire Tested: P3AS09R35B2750DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35B2750DE010 E3DL1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 606.0 lumens
Efficiency: N/A
Efficacy: 46.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283213

CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283213

CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90		
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70		
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66		
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	64		
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	305633
5°	293748
10°	255929
15°	196028
20°	131145
25°	79359
30°	45526
35°	25458
40°	13540
45°	6977
50°	3343
55°	2638
60°	2544
65°	2075
70°	2244
75°	1949
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6977 cd/sqm

TEST NUMBER: P1283213

CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.4	20.0
10°-20°	235.3	38.8
20°-30°	154.0	25.4
30°-40°	62.5	10.3
40°-50°	18.8	3.1
50°-60°	6.4	1.1
60°-70°	4.3	0.7
70°-80°	2.5	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	510.7	84.3
0°-40°	573.2	94.6
0°-60°	598.3	98.7
0°-90°	606.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1394	
5°	1334	121
15°	864	235
25°	328	154
35°	95	62
45°	22	19
55°	7	6
65°	4	4
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1283213

CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1393.8
1°	1391.5
2°	1385.2
3°	1372.5
4°	1357.5
5°	1334.5
6°	1305.6
7°	1273.4
8°	1237.0
9°	1195.5
10°	1149.4
11°	1098.1
12°	1044.5
13°	984.6
14°	927.5
15°	863.5
17.5°	708.4
20°	562.0
22.5°	432.3
25°	328.0
27.5°	244.4
30°	179.8
32.5°	132.0
35°	95.1
37.5°	67.4
40°	47.3
42.5°	32.9
45°	22.5
47.5°	15.0
50°	9.8
52.5°	7.5
55°	6.9
57.5°	6.3
60°	5.8
62.5°	5.2
65°	4.0
67.5°	3.5
70°	3.5
72.5°	2.9
75°	2.3
77.5°	1.7
80°	1.7
82.5°	1.2
85°	0.6
87.5°	0.6



TEST NUMBER: P1283213

CATALOG NUMBER: P3AS09R35B2750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)