

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284150

Luminaire Tested: P3AS09R70B2750DE010 E3CB1MMS_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70B2750DE010 E3CB1MMS_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 80CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 734.0 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284150

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MMS_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284150

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MMS_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94		93
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91	89	87		85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80		78
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80	77	74		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75	71	68		66
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70	66	63		61
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66	62	58		57
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62	57	54		53
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58	54	50		49
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55	50	47		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145756
5°	139071
10°	132329
15°	128786
20°	124027
25°	117394
30°	109181
35°	91711
40°	59111
45°	27476
50°	7198
55°	1797
60°	1798
65°	1505
70°	1475
75°	1525
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27476 cd/sqm

TEST NUMBER: P1284150

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MMS_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	8.1
10°-20°	159.4	21.7
20°-30°	222.7	30.3
30°-40°	206.5	28.1
40°-50°	74.0	10.1
50°-60°	6.3	0.9
60°-70°	3.1	0.4
70°-80°	2.0	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.3	60.1
0°-40°	647.8	88.3
0°-60°	728.1	99.2
0°-90°	734.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	734.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	665	
5°	632	59
15°	567	159
25°	485	223
35°	343	206
45°	89	74
55°	5	6
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1284150

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MMS_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	664.7
2.5°	654.7
5°	631.8
7.5°	610.7
10°	594.3
12.5°	580.8
15°	567.3
17.5°	550.9
20°	531.5
22.5°	509.2
25°	485.2
27.5°	460.5
30°	431.2
32.5°	393.6
35°	342.6
37.5°	277.5
40°	206.5
42.5°	140.8
45°	88.6
47.5°	49.3
50°	21.1
52.5°	7.0
55°	4.7
57.5°	4.1
60°	4.1
62.5°	3.5
65°	2.9
67.5°	2.9
70°	2.3
72.5°	2.3
75°	1.8
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)