

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284172

Luminaire Tested: P3AS09R70B2750DE010 E3D1H_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284172
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70B2750DE010 E3D1H_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 698.1 lumens
Efficiency: N/A
Efficacy: 53.3 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284172

CATALOG NUMBER: P3AS09R70B2750DE010 E3D1H_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1284172

CATALOG NUMBER: P3AS09R70B2750DE010 E3D1H_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79		
4	95	87	81	77	94	86	81	76	84	79	76	82	78	75	80	77	74	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135713
5°	127977
10°	121352
15°	119161
20°	114857
25°	108272
30°	107510
35°	93612
40°	60571
45°	28623
50°	4025
55°	344
60°	263
65°	311
70°	192
75°	254
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28623 cd/sqm

TEST NUMBER: P1284172

CATALOG NUMBER: P3AS09R70B2750DE010 E3D1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	7.8
10°-20°	147.4	21.1
20°-30°	208.5	29.9
30°-40°	209.6	30.0
40°-50°	75.4	10.8
50°-60°	2.0	0.3
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	410.2	58.8
0°-40°	619.8	88.8
0°-60°	697.2	99.9
0°-90°	698.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	698.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	619	
5°	581	54
15°	525	147
25°	448	209
35°	350	210
45°	92	75
55°	1	2
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1284172

CATALOG NUMBER: P3AS09R70B2750DE010 E3D1H_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	618.9
1°	617.2
2°	611.8
3°	603.2
4°	592.3
5°	581.4
6°	571.1
7°	563.0
8°	555.9
9°	550.1
10°	545.0
11°	540.7
12°	536.7
13°	532.6
14°	528.9
15°	524.9
16°	520.0
17°	514.9
18°	508.6
19°	500.8
20°	492.2
21°	482.8
22°	473.3
23°	464.1
24°	455.2
25°	447.5
26°	442.1
27°	437.8
28°	434.3
29°	430.3
30°	424.6
31°	416.3
32°	404.5
32.5°	397.9
33°	389.0
34°	371.5
35°	349.7
36°	325.7
37°	298.4
37.5°	285.8
38°	268.6
39°	237.9
40°	211.6
42.5°	146.5
45°	92.3

TEST NUMBER: P1284172

CATALOG NUMBER: P3AS09R70B2750DE010 E3D1H_2700K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	49.6
50°	11.8
52.5°	1.4
55°	0.9
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)