

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283246

Luminaire Tested: P3AS09R35B2750DE010 E3DLD1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283246
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35B2750DE010 E3DLD1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 507.0 lumens
Efficiency: N/A
Efficacy: 38.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283246

CATALOG NUMBER: P3AS09R35B2750DE010 E3DLD1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283246

CATALOG NUMBER: P3AS09R35B2750DE010 E3DLD1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115824
5°	113361
10°	106166
15°	95301
20°	82887
25°	70649
30°	59174
35°	47141
40°	34064
45°	21553
50°	11769
55°	8143
60°	7675
65°	7160
70°	6860
75°	5846
80°	5556
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21553 cd/sqm

TEST NUMBER: P1283246

CATALOG NUMBER: P3AS09R35B2750DE010 E3DLD1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	9.5
10°-20°	116.8	23.0
20°-30°	133.9	26.4
30°-40°	109.2	21.5
40°-50°	55.1	10.9
50°-60°	20.5	4.0
60°-70°	13.7	2.7
70°-80°	7.6	1.5
80°-90°	2.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.6	58.9
0°-40°	407.8	80.4
0°-60°	483.4	95.3
0°-90°	507.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	507.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	528	
5°	515	48
15°	420	117
25°	292	134
35°	176	109
45°	70	55
55°	21	20
65°	14	14
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P1283246

CATALOG NUMBER: P3AS09R35B2750DE010 E3DLD1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	528.2
1°	527.5
2°	526.3
3°	523.8
4°	520.0
5°	515.0
6°	508.7
7°	502.5
8°	494.3
9°	486.2
10°	476.8
11°	466.8
12°	456.1
13°	444.2
14°	431.7
15°	419.8
17.5°	387.8
20°	355.2
22.5°	322.0
25°	292.0
27.5°	262.5
30°	233.7
32.5°	204.9
35°	176.1
37.5°	147.2
40°	119.0
42.5°	92.7
45°	69.5
47.5°	50.1
50°	34.5
52.5°	25.1
55°	21.3
57.5°	19.4
60°	17.5
62.5°	15.7
65°	13.8
67.5°	11.9
70°	10.7
72.5°	8.8
75°	6.9
77.5°	5.6
80°	4.4
82.5°	3.1
85°	1.9
87.5°	1.3



TEST NUMBER: P1283246

CATALOG NUMBER: P3AS09R35B2750DE010 E3DLD1WMH_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)