

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284306

Luminaire Tested: P3AS13R15B2750DE010 E3D1LI_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15B2750DE010 E3D1LI_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 80CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1062.0 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284306

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1LI_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284306

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1LI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	99	98	97	96	95	94	93	92	91	90	89	88
2	112	109	107	105	110	108	105	103	105	103	101	102	100	99	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85
3	110	106	102	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94	93	92	91	90	89	88	87	86	85	84	83
4	107	102	99	96	106	101	98	96	99	97	95	98	96	94	96	94	93	92	91	90	89	88	87	86	85	84	83	82	81
5	105	100	96	94	103	99	96	93	97	94	92	96	93	92	94	93	91	90	89	88	87	86	85	84	83	82	81	80	79
6	102	97	94	91	101	96	93	91	95	92	90	94	92	90	93	91	89	88	87	86	85	84	83	82	81	80	79	78	77
7	100	95	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	87	86	85	84	83	82	81	80	79	78	77	76
8	98	93	89	87	97	92	89	87	91	89	87	91	88	86	90	88	86	85	84	83	82	81	80	79	78	77	76	75	74
9	96	91	88	85	96	91	87	85	90	87	85	89	87	85	89	86	85	84	83	82	81	80	79	78	77	76	75	74	73
10	95	89	86	84	94	89	86	84	88	85	83	88	85	83	87	85	83	82	81	80	79	78	77	76	75	74	73	72	71

AVERAGE LUMINANCE (cd/sqm):

0°	2022316
5°	1649060
10°	807623
15°	247198
20°	104682
25°	47350
30°	18459
35°	8513
40°	2662
45°	992
50°	409
55°	153
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 992 cd/sqm

TEST NUMBER: P1284306

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	583.1	54.9
10°-20°	357.8	33.7
20°-30°	96.1	9.1
30°-40°	21.2	2.0
40°-50°	3.0	0.3
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1037.1	97.7
0°-40°	1058.3	99.6
0°-60°	1061.7	100.0
0°-90°	1062.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1062.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9222	
5°	7492	583
15°	1089	358
25°	196	96
35°	32	21
45°	3	3
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1284306

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1LI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	9222.5
1°	9164.9
2°	8980.1
3°	8647.1
4°	8145.7
5°	7491.7
6°	6752.0
7°	5928.1
8°	5171.0
9°	4368.4
10°	3627.1
11°	2893.4
12°	2226.1
13°	1712.3
14°	1355.5
15°	1088.9
17.5°	674.9
20°	448.6
22.5°	302.0
25°	195.7
27.5°	116.0
30°	72.9
32.5°	49.1
35°	31.8
37.5°	17.7
40°	9.3
42.5°	5.2
45°	3.2
47.5°	2.0
50°	1.2
52.5°	0.8
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1284306

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1LI_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)