

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284320

Luminaire Tested: P3AS13R15B2750DE010 E3D1WMH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284320
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15B2750DE010 E3D1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 80CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 995.0 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284320

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284320

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	99	98	97	96	95	94	93	92	91	90	89	88
2	112	109	107	105	110	108	105	103	105	103	101	102	100	99	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85
3	110	106	102	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94	93	92	91	90	89	88	87	86	85	84	83
4	107	102	99	96	105	101	98	96	99	97	95	98	96	94	96	94	93	92	91	90	89	88	87	86	85	84	83	82	81
5	105	100	96	94	103	99	96	93	97	94	92	96	93	92	94	93	91	90	89	88	87	86	85	84	83	82	81	80	79
6	102	97	94	91	101	96	93	91	95	92	90	94	92	90	93	91	89	88	87	86	85	84	83	82	81	80	79	78	77
7	100	95	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	87	86	85	84	83	82	81	80	79	78	77	76
8	98	93	89	87	97	92	89	87	91	89	87	91	88	86	90	88	86	85	84	83	82	81	80	79	78	77	76	75	74
9	96	91	88	85	96	91	87	85	90	87	85	89	87	85	88	86	85	84	83	82	81	80	79	78	77	76	75	74	73
10	95	89	86	84	94	89	86	84	88	85	83	88	85	83	87	85	83	82	81	80	79	78	77	76	75	74	73	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1894739
5°	1545032
10°	756655
15°	231602
20°	98079
25°	44374
30°	17294
35°	7977
40°	2490
45°	930
50°	375
55°	153
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 930 cd/sqm

TEST NUMBER: P1284320

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	546.4	54.9
10°-20°	335.3	33.7
20°-30°	90.1	9.1
30°-40°	19.8	2.0
40°-50°	2.8	0.3
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	971.7	97.7
0°-40°	991.5	99.6
0°-60°	994.8	100.0
0°-90°	995.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	995.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8641	
5°	7019	546
15°	1020	335
25°	183	90
35°	30	20
45°	3	3
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1284320

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	8640.7
1°	8586.7
2°	8413.6
3°	8101.5
4°	7631.8
5°	7019.1
6°	6326.0
7°	5554.1
8°	4844.8
9°	4092.8
10°	3398.2
11°	2710.8
12°	2085.7
13°	1604.2
14°	1270.0
15°	1020.2
17.5°	632.3
20°	420.3
22.5°	283.0
25°	183.4
27.5°	108.7
30°	68.3
32.5°	46.0
35°	29.8
37.5°	16.6
40°	8.7
42.5°	4.9
45°	3.0
47.5°	1.9
50°	1.1
52.5°	0.8
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1284320

CATALOG NUMBER: P3AS13R15B2750DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)