

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283347

Luminaire Tested: P3AS09R40B2750DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40B2750DE010 E3DL1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 334.0 lumens
Efficiency: N/A
Efficacy: 25.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283347

CATALOG NUMBER: P3AS09R40B2750DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1283347

CATALOG NUMBER: P3AS09R40B2750DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147795
5°	143495
10°	130214
15°	107583
20°	77613
25°	48003
30°	25979
35°	13438
40°	7299
45°	4093
50°	2047
55°	1529
60°	1403
65°	1349
70°	1282
75°	1186
80°	1137
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4093 cd/sqm

TEST NUMBER: P1283347

CATALOG NUMBER: P3AS09R40B2750DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.1	18.0
10°-20°	129.0	38.6
20°-30°	92.1	27.6
30°-40°	33.9	10.1
40°-50°	10.7	3.2
50°-60°	3.7	1.1
60°-70°	2.6	0.8
70°-80°	1.5	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.2	84.2
0°-40°	315.1	94.3
0°-60°	329.5	98.6
0°-90°	334.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	334.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	674	
5°	652	60
15°	474	129
25°	198	92
35°	50	34
45°	13	11
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1283347

CATALOG NUMBER: P3AS09R40B2750DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	674.0
2.5°	668.8
5°	651.9
7.5°	623.8
10°	584.8
12.5°	535.2
15°	473.9
17.5°	405.1
20°	332.6
22.5°	261.2
25°	198.4
27.5°	145.6
30°	102.6
32.5°	72.0
35°	50.2
37.5°	35.5
40°	25.5
42.5°	18.3
45°	13.2
47.5°	8.9
50°	6.0
52.5°	4.3
55°	4.0
57.5°	3.7
60°	3.2
62.5°	2.9
65°	2.6
67.5°	2.3
70°	2.0
72.5°	1.7
75°	1.4
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)