

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284384

Luminaire Tested: P3AS13R15B2750DE010 E3DLP1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15B2750DE010 E3DLP1GPH_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 80CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 234.0 lumens
Efficiency: N/A
Efficacy: 12.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284384

CATALOG NUMBER: P3AS13R15B2750DE010 E3DLP1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1284384

CATALOG NUMBER: P3AS13R15B2750DE010 E3DLP1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97	96	95		93
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92	90	88		86
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82		80
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82	79	77		75
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78	75	72		70
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68		66
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71	67	64		62
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60		59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57		56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	57	54		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100913
5°	93264
10°	74459
15°	56255
20°	42820
25°	32639
30°	23371
35°	15258
40°	9360
45°	5644
50°	3753
55°	2906
60°	2500
65°	2179
70°	1923
75°	1949
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5644 cd/sqm

TEST NUMBER: P1284384

CATALOG NUMBER: P3AS13R15B2750DE010 E3DLP1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	16.0
10°-20°	69.2	29.6
20°-30°	61.7	26.3
30°-40°	36.5	15.6
40°-50°	15.0	6.4
50°-60°	7.0	3.0
60°-70°	4.3	1.8
70°-80°	2.3	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	168.4	72.0
0°-40°	204.9	87.6
0°-60°	226.9	97.0
0°-90°	234.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	234.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	424	38
15°	248	69
25°	135	62
35°	57	36
45°	18	15
55°	8	7
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1284384

CATALOG NUMBER: P3AS13R15B2750DE010 E3DLP1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	460.2
1°	459.0
2°	455.6
3°	448.8
4°	437.4
5°	423.7
6°	408.9
7°	391.4
8°	373.2
9°	354.5
10°	334.4
12.5°	288.4
15°	247.8
17.5°	212.8
20°	183.5
22.5°	157.7
25°	134.9
27.5°	112.9
30°	92.3
32.5°	73.7
35°	57.0
37.5°	43.7
40°	32.7
42.5°	24.3
45°	18.2
47.5°	14.1
50°	11.0
52.5°	9.1
55°	7.6
57.5°	6.5
60°	5.7
62.5°	4.9
65°	4.2
67.5°	3.8
70°	3.0
72.5°	2.7
75°	2.3
77.5°	1.5
80°	1.1
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)