

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283385

Luminaire Tested: P3AS09R40B2750DE010 E3DLD1H_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40B2750DE010 E3DLD1H_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 80CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 524.0 lumens
Efficiency: N/A
Efficacy: 40.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283385

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1H_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283385

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1H_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	112	109	106	104		110	107	104	102		103	101	99		99	98	96		96	94	93		91			
2	106	100	96	92		104	98	94	91		95	92	89		92	89	87		89	87	85		83			
3	100	92	87	82		98	91	86	81		88	84	80		86	82	79		83	80	78		76			
4	94	85	79	74		92	84	78	74		82	77	73		80	75	72		78	74	71		69			
5	89	79	73	68		87	78	72	67		76	71	67		75	70	66		73	69	66		64			
6	84	74	67	62		82	73	67	62		71	66	61		70	65	61		68	64	61		59			
7	79	69	62	57		78	68	62	57		67	61	57		65	60	57		64	60	56		55			
8	75	64	58	53		74	64	57	53		63	57	53		62	56	53		61	56	52		51			
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49		48			
10	67	57	51	46		66	56	50	46		56	50	46		55	50	46		54	49	46		45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117622
5°	115496
10°	108860
15°	98888
20°	86878
25°	74182
30°	61452
35°	47382
40°	33720
45°	22731
50°	12383
55°	8755
60°	8245
65°	7627
70°	6796
75°	6439
80°	5177
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22731 cd/sqm

TEST NUMBER: P1283385

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1H_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.9	9.3
10°-20°	121.3	23.2
20°-30°	140.3	26.8
30°-40°	110.5	21.1
40°-50°	56.7	10.8
50°-60°	21.7	4.1
60°-70°	14.4	2.7
70°-80°	7.8	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	310.6	59.3
0°-40°	421.1	80.4
0°-60°	499.5	95.3
0°-90°	524.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	524.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	536	
5°	525	49
15°	436	121
25°	307	140
35°	177	111
45°	73	57
55°	23	22
65°	15	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1283385

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1H_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	536.4
2.5°	533.5
5°	524.7
7.5°	509.5
10°	488.9
12.5°	464.9
15°	435.6
17.5°	405.1
20°	372.3
22.5°	338.9
25°	306.6
27.5°	274.4
30°	242.7
32.5°	210.5
35°	177.0
37.5°	146.0
40°	117.8
42.5°	93.8
45°	73.3
47.5°	53.3
50°	36.3
52.5°	26.4
55°	22.9
57.5°	20.5
60°	18.8
62.5°	16.4
65°	14.7
67.5°	12.3
70°	10.6
72.5°	8.8
75°	7.6
77.5°	5.9
80°	4.1
82.5°	3.5
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)