

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283386

Luminaire Tested: P3AS09R40B2750DE010 E3DLD1H_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40B2750DE010 E3DLD1H_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 80CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 560.0 lumens
Efficiency: N/A
Efficacy: 42.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283386
CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1H_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283386
 CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1H_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125714
5°	123420
10°	116342
15°	105676
20°	92828
25°	79287
30°	65681
35°	50647
40°	36039
45°	24282
50°	13236
55°	9328
60°	8771
65°	8146
70°	7245
75°	6863
80°	5556
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24282 cd/sqm



TEST NUMBER: P1283386

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1H_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	9.3
10°-20°	129.7	23.2
20°-30°	149.9	26.8
30°-40°	118.1	21.1
40°-50°	60.6	10.8
50°-60°	23.2	4.1
60°-70°	15.3	2.7
70°-80°	8.3	1.5
80°-90°	2.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	331.9	59.3
0°-40°	450.0	80.4
0°-60°	533.8	95.3
0°-90°	560.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	560.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	573	
5°	561	52
15°	466	130
25°	328	150
35°	189	118
45°	78	61
55°	24	23
65°	16	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1283386
CATALOG NUMBER: P3AS09R40B2750DE010 E3DLD1H_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	573.3
2.5°	570.1
5°	560.7
7.5°	544.5
10°	522.5
12.5°	496.8
15°	465.5
17.5°	432.9
20°	397.8
22.5°	362.1
25°	327.7
27.5°	293.2
30°	259.4
32.5°	224.9
35°	189.2
37.5°	156.0
40°	125.9
42.5°	100.2
45°	78.3
47.5°	57.0
50°	38.8
52.5°	28.2
55°	24.4
57.5°	21.9
60°	20.0
62.5°	17.5
65°	15.7
67.5°	13.2
70°	11.3
72.5°	9.4
75°	8.1
77.5°	6.3
80°	4.4
82.5°	3.8
85°	1.9
87.5°	1.3
90°	0.0

(END OF REPORT)