

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283428

Luminaire Tested: P3AS09R40B2750DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283428
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40B2750DE010 E3DLP1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 672.0 lumens
Efficiency: N/A
Efficacy: 51.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283428

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283428

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLP1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84		
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80		
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76		
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72		
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69		
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65		
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63		
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	297345
5°	288707
10°	262008
15°	216437
20°	156137
25°	96562
30°	52287
35°	27010
40°	14685
45°	8218
50°	4128
55°	3097
60°	2763
65°	2698
70°	2565
75°	2457
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8218 cd/sqm

TEST NUMBER: P1283428

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLP1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	18.0
10°-20°	259.6	38.6
20°-30°	185.3	27.6
30°-40°	68.2	10.1
40°-50°	21.5	3.2
50°-60°	7.5	1.1
60°-70°	5.1	0.8
70°-80°	3.0	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.8	84.2
0°-40°	634.0	94.3
0°-60°	662.9	98.7
0°-90°	672.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	672.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1356	
5°	1312	121
15°	953	260
25°	399	185
35°	101	68
45°	26	21
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1283428

CATALOG NUMBER: P3AS09R40B2750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1356.0
2.5°	1345.7
5°	1311.6
7.5°	1255.1
10°	1176.7
12.5°	1076.9
15°	953.4
17.5°	815.0
20°	669.1
22.5°	525.5
25°	399.1
27.5°	293.0
30°	206.5
32.5°	144.8
35°	100.9
37.5°	71.5
40°	51.3
42.5°	36.9
45°	26.5
47.5°	17.9
50°	12.1
52.5°	8.7
55°	8.1
57.5°	7.5
60°	6.3
62.5°	5.8
65°	5.2
67.5°	4.6
70°	4.0
72.5°	3.5
75°	2.9
77.5°	2.3
80°	1.7
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)