

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284497

Luminaire Tested: P3AS13R20B2750DE010 E3DL1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20B2750DE010 E3DL1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 793.9 lumens
Efficiency: N/A
Efficacy: 41.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284497
CATALOG NUMBER: P3AS13R20B2750DE010 E3DL1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1284497

CATALOG NUMBER: P3AS13R20B2750DE010 E3DL1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	92	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	610894
5°	555314
10°	410413
15°	253872
20°	144983
25°	82771
30°	46412
35°	25243
40°	13826
45°	7598
50°	4435
55°	3211
60°	3026
65°	2802
70°	2436
75°	2626
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7598 cd/sqm



TEST NUMBER: P1284497

CATALOG NUMBER: P3AS13R20B2750DE010 E3DL1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.5	27.5
10°-20°	311.9	39.3
20°-30°	162.8	20.5
30°-40°	62.9	7.9
40°-50°	20.4	2.6
50°-60°	8.0	1.0
60°-70°	5.3	0.7
70°-80°	3.1	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	693.1	87.3
0°-40°	756.0	95.2
0°-60°	784.5	98.8
0°-90°	793.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2786	
5°	2523	218
15°	1118	312
25°	342	163
35°	94	63
45°	24	20
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1284497
CATALOG NUMBER: P3AS13R20B2750DE010 E3DL1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2785.9
1°	2780.5
2°	2747.5
3°	2696.9
4°	2618.7
5°	2522.8
6°	2409.3
7°	2283.5
8°	2137.7
9°	1995.8
10°	1843.2
12.5°	1465.0
15°	1118.3
17.5°	836.8
20°	621.3
22.5°	460.2
25°	342.1
27.5°	252.4
30°	183.3
32.5°	132.7
35°	94.3
37.5°	68.3
40°	48.3
42.5°	34.5
45°	24.5
47.5°	17.6
50°	13.0
52.5°	10.0
55°	8.4
57.5°	7.7
60°	6.9
62.5°	6.1
65°	5.4
67.5°	4.6
70°	3.8
72.5°	3.8
75°	3.1
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)