

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283475

Luminaire Tested: P3AS09R45B2750DE010 E3DL1GPH\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1283475  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45B2750DE010 E3DL1GPH\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 321.0 lumens  
Efficiency: N/A  
Efficacy: 24.5 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1283475

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1GPH\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1283475

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1GPH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     |     | 0   |     |     |     | 0   |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 94  |
| 2   | 109 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 94  | 96  | 94  | 92  | 93  | 91  | 90  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 88  |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 94  | 90  | 87  | 91  | 88  | 86  | 89  | 86  | 84  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 82  | 89  | 85  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  | 82  | 79  | 76  | 81  | 78  | 75  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  |
| 6   | 90  | 82  | 76  | 73  | 89  | 81  | 76  | 72  | 80  | 75  | 72  | 78  | 74  | 71  | 77  | 74  | 71  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  | 70  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  |
| 8   | 83  | 74  | 68  | 65  | 82  | 73  | 68  | 64  | 72  | 68  | 64  | 71  | 67  | 64  | 70  | 67  | 64  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 61  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 58  | 65  | 61  | 58  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 120539 |
| 5°  | 117719 |
| 10° | 108214 |
| 15° | 91692  |
| 20° | 71150  |
| 25° | 49721  |
| 30° | 31321  |
| 35° | 18444  |
| 40° | 10448  |
| 45° | 5086   |
| 50° | 1774   |
| 55° | 1415   |
| 60° | 1403   |
| 65° | 1349   |
| 70° | 1282   |
| 75° | 1186   |
| 80° | 1137   |
| 85° | 755    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 5086 cd/sqm

TEST NUMBER: P1283475

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1GPH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 49.5   | 15.4      |
| 10°-20°   | 110.9  | 34.6      |
| 20°-30°   | 94.2   | 29.3      |
| 30°-40°   | 44.9   | 14.0      |
| 40°-50°   | 13.6   | 4.2       |
| 50°-60°   | 3.4    | 1.1       |
| 60°-70°   | 2.6    | 0.8       |
| 70°-80°   | 1.5    | 0.5       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 254.6  | 79.3      |
| 0°-40°    | 299.5  | 93.3      |
| 0°-60°    | 316.5  | 98.6      |
| 0°-90°    | 321.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 321.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 550 |      |
| 5°  | 535 | 50   |
| 15° | 404 | 111  |
| 25° | 206 | 94   |
| 35° | 69  | 45   |
| 45° | 16  | 14   |
| 55° | 4   | 3    |
| 65° | 3   | 3    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P1283475

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1GPH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 549.7 |
| 2.5°  | 546.3 |
| 5°    | 534.8 |
| 7.5°  | 515.0 |
| 10°   | 486.0 |
| 12.5° | 447.5 |
| 15°   | 403.9 |
| 17.5° | 355.4 |
| 20°   | 304.9 |
| 22.5° | 253.5 |
| 25°   | 205.5 |
| 27.5° | 161.9 |
| 30°   | 123.7 |
| 32.5° | 93.0  |
| 35°   | 68.9  |
| 37.5° | 50.8  |
| 40°   | 36.5  |
| 42.5° | 25.3  |
| 45°   | 16.4  |
| 47.5° | 9.2   |
| 50°   | 5.2   |
| 52.5° | 4.0   |
| 55°   | 3.7   |
| 57.5° | 3.4   |
| 60°   | 3.2   |
| 62.5° | 2.9   |
| 65°   | 2.6   |
| 67.5° | 2.3   |
| 70°   | 2.0   |
| 72.5° | 1.7   |
| 75°   | 1.4   |
| 77.5° | 1.1   |
| 80°   | 0.9   |
| 82.5° | 0.6   |
| 85°   | 0.3   |
| 87.5° | 0.3   |
| 90°   | 0.0   |

(END OF REPORT)