

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284540

Luminaire Tested: P3AS13R20B2750DE010 E3DLP1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284540
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20B2750DE010 E3DLP1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 4000K CCT AND, 80CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 796.0 lumens
Efficiency: N/A
Efficacy: 41.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284540

CATALOG NUMBER: P3AS13R20B2750DE010 E3DLP1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284540

CATALOG NUMBER: P3AS13R20B2750DE010 E3DLP1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87			
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83			
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79			
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76			
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73			
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71			
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68			
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	612429
5°	556723
10°	411437
15°	254530
20°	145356
25°	82989
30°	46539
35°	25324
40°	13855
45°	7629
50°	4469
55°	3250
60°	3026
65°	2802
70°	2436
75°	2626
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7629 cd/sqm

TEST NUMBER: P1284540

CATALOG NUMBER: P3AS13R20B2750DE010 E3DLP1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.0	27.5
10°-20°	312.6	39.3
20°-30°	163.2	20.5
30°-40°	63.1	7.9
40°-50°	20.5	2.6
50°-60°	8.1	1.0
60°-70°	5.3	0.7
70°-80°	3.1	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.9	87.3
0°-40°	757.9	95.2
0°-60°	786.5	98.8
0°-90°	796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2793	
5°	2529	219
15°	1121	313
25°	343	163
35°	95	63
45°	25	20
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1284540

CATALOG NUMBER: P3AS13R20B2750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2792.9
1°	2787.5
2°	2754.5
3°	2703.7
4°	2625.3
5°	2529.2
6°	2415.3
7°	2289.2
8°	2143.1
9°	2000.9
10°	1847.8
12.5°	1468.7
15°	1121.2
17.5°	838.9
20°	622.9
22.5°	461.4
25°	343.0
27.5°	253.0
30°	183.8
32.5°	133.0
35°	94.6
37.5°	68.4
40°	48.4
42.5°	34.6
45°	24.6
47.5°	17.7
50°	13.1
52.5°	10.0
55°	8.5
57.5°	7.7
60°	6.9
62.5°	6.2
65°	5.4
67.5°	4.6
70°	3.8
72.5°	3.8
75°	3.1
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)