

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283483

Luminaire Tested: P3AS09R45B2750DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45B2750DE010 E3DL1LI_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 645.0 lumens
Efficiency: N/A
Efficacy: 49.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283483

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283483

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94						
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88						
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83						
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78						
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74						
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70						
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66						
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62						
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59						
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	242217
5°	236539
10°	217453
15°	184246
20°	142952
25°	99925
30°	62946
35°	37049
40°	20982
45°	10203
50°	3548
55°	2867
60°	2763
65°	2698
70°	2565
75°	2457
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10203 cd/sqm

TEST NUMBER: P1283483

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	15.4
10°-20°	222.9	34.6
20°-30°	189.2	29.3
30°-40°	90.3	14.0
40°-50°	27.2	4.2
50°-60°	6.9	1.1
60°-70°	5.1	0.8
70°-80°	3.0	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.6	79.3
0°-40°	601.9	93.3
0°-60°	636.0	98.6
0°-90°	645.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	645.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1105	
5°	1075	99
15°	812	223
25°	413	189
35°	138	90
45°	33	27
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1283483

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1104.6
2.5°	1097.7
5°	1074.6
7.5°	1034.8
10°	976.6
12.5°	899.3
15°	811.6
17.5°	714.1
20°	612.6
22.5°	509.3
25°	413.0
27.5°	325.3
30°	248.6
32.5°	186.9
35°	138.4
37.5°	102.1
40°	73.3
42.5°	50.8
45°	32.9
47.5°	18.5
50°	10.4
52.5°	8.1
55°	7.5
57.5°	6.9
60°	6.3
62.5°	5.8
65°	5.2
67.5°	4.6
70°	4.0
72.5°	3.5
75°	2.9
77.5°	2.3
80°	1.7
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)