

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284547

Luminaire Tested: P3AS13R20B2750DE010 E3PHLD1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20B2750DE010 E3PHLD1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 528.0 lumens
Efficiency: N/A
Efficacy: 27.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284547

CATALOG NUMBER: P3AS13R20B2750DE010 E3PHLD1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1284547

CATALOG NUMBER: P3AS13R20B2750DE010 E3PHLD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	85	82	80
3	98	90	83	78	95	88	82	78	85	81	77		83	79	75		80	77	74	72
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75	71	67	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	81	70	63	58	79	70	63	58	68	62	58		66	61	57		65	60	57	55
7	76	66	59	54	75	65	58	53	64	58	53		62	57	53		61	56	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54	49	46	44
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51	46	43	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149747
5°	139115
10°	117789
15°	92214
20°	72573
25°	57850
30°	46513
35°	37932
40°	31373
45°	26421
50°	22652
55°	19459
60°	16972
65°	14943
70°	12759
75°	11268
80°	8334
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 26421 cd/sqm

TEST NUMBER: P1284547

CATALOG NUMBER: P3AS13R20B2750DE010 E3PHLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	10.8
10°-20°	113.7	21.5
20°-30°	110.4	20.9
30°-40°	89.2	16.9
40°-50°	66.3	12.6
50°-60°	46.1	8.7
60°-70°	28.8	5.5
70°-80°	14.0	2.7
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.2	53.3
0°-40°	370.4	70.2
0°-60°	482.8	91.4
0°-90°	528.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	683	
5°	632	57
15°	406	114
25°	239	110
35°	142	89
45°	85	66
55°	51	46
65°	29	29
75°	13	14
85°	2	2
90°	0	

TEST NUMBER: P1284547

CATALOG NUMBER: P3AS13R20B2750DE010 E3PHLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	682.9
2.5°	667.4
5°	632.0
7.5°	584.4
10°	529.0
12.5°	468.2
15°	406.2
17.5°	355.3
20°	311.0
22.5°	272.3
25°	239.1
27.5°	210.3
30°	183.7
32.5°	161.6
35°	141.7
37.5°	124.0
40°	109.6
42.5°	96.3
45°	85.2
47.5°	75.3
50°	66.4
52.5°	58.7
55°	50.9
57.5°	44.3
60°	38.7
62.5°	34.3
65°	28.8
67.5°	24.3
70°	19.9
72.5°	16.6
75°	13.3
77.5°	10.0
80°	6.6
82.5°	3.3
85°	2.2
87.5°	0.0
90°	0.0

(END OF REPORT)