

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283491

Luminaire Tested: P3AS09R45B2750DE010 E3DL1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283491
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45B2750DE010 E3DL1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 80CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 700.0 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283491

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283491

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94						
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88						
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83						
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78						
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74						
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70						
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66						
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62						
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59						
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	262874
5°	256724
10°	235979
15°	199956
20°	155133
25°	108442
30°	68314
35°	40207
40°	22757
45°	11071
50°	3855
55°	3097
60°	3026
65°	2906
70°	2821
75°	2626
80°	2399
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11071 cd/sqm

TEST NUMBER: P1283491

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.0	15.4
10°-20°	241.9	34.6
20°-30°	205.4	29.3
30°-40°	98.0	14.0
40°-50°	29.5	4.2
50°-60°	7.5	1.1
60°-70°	5.6	0.8
70°-80°	3.3	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	555.2	79.3
0°-40°	653.2	93.3
0°-60°	690.2	98.6
0°-90°	700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1199	
5°	1166	108
15°	881	242
25°	448	205
35°	150	98
45°	36	30
55°	8	7
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1283491

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1198.8
2.5°	1191.3
5°	1166.3
7.5°	1123.1
10°	1059.8
12.5°	975.9
15°	880.8
17.5°	775.0
20°	664.8
22.5°	552.8
25°	448.2
27.5°	353.1
30°	269.8
32.5°	202.8
35°	150.2
37.5°	110.8
40°	79.5
42.5°	55.1
45°	35.7
47.5°	20.0
50°	11.3
52.5°	8.8
55°	8.1
57.5°	7.5
60°	6.9
62.5°	6.3
65°	5.6
67.5°	5.0
70°	4.4
72.5°	3.8
75°	3.1
77.5°	2.5
80°	1.9
82.5°	1.3
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)