

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283493

Luminaire Tested: P3AS09R45B2750DE010 E3DL1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283493
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45B2750DE010 E3DL1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 416.0 lumens
Efficiency: N/A
Efficacy: 31.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283493

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283493

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86	83	81	79
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81	78	75	74
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	66	64
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69	65	61	60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65	61	58	56
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62	58	55	53
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123916
5°	121087
10°	111688
15°	97117
20°	79784
25°	62084
30°	45855
35°	32257
40°	20123
45°	10916
50°	5902
55°	5085
60°	4561
65°	3891
70°	3334
75°	3389
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10916 cd/sqm

TEST NUMBER: P1283493

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	12.2
10°-20°	118.3	28.4
20°-30°	117.4	28.2
30°-40°	75.6	18.2
40°-50°	29.1	7.0
50°-60°	11.8	2.8
60°-70°	7.5	1.8
70°-80°	4.0	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.6	68.9
0°-40°	362.3	87.1
0°-60°	403.2	96.9
0°-90°	416.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	416.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	565	
5°	550	51
15°	428	118
25°	257	117
35°	120	76
45°	35	29
55°	13	12
65°	8	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283493

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	565.1
2.5°	562.2
5°	550.1
7.5°	529.3
10°	501.6
12.5°	467.1
15°	427.8
17.5°	385.2
20°	341.9
22.5°	298.1
25°	256.6
27.5°	217.4
30°	181.1
32.5°	149.3
35°	120.5
37.5°	94.6
40°	70.3
42.5°	50.7
45°	35.2
47.5°	23.6
50°	17.3
52.5°	14.4
55°	13.3
57.5°	11.5
60°	10.4
62.5°	8.6
65°	7.5
67.5°	6.3
70°	5.2
72.5°	4.6
75°	4.0
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)