

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283500

Luminaire Tested: P3AS09R45B2750DE010 E3DL1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45B2750DE010 E3DL1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 656.0 lumens
Efficiency: N/A
Efficacy: 50.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283500

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283500

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96		94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90		88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84		83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79		78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75		74
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77	74	71		70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67		66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64		62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61		59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246340
5°	240567
10°	221149
15°	187379
20°	145379
25°	101619
30°	64010
35°	37691
40°	21326
45°	10358
50°	3616
55°	2906
60°	2851
65°	2750
70°	2629
75°	2457
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10358 cd/sqm

TEST NUMBER: P1283500

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.2	15.4
10°-20°	226.7	34.6
20°-30°	192.5	29.3
30°-40°	91.8	14.0
40°-50°	27.7	4.2
50°-60°	7.0	1.1
60°-70°	5.2	0.8
70°-80°	3.1	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.3	79.3
0°-40°	612.1	93.3
0°-60°	646.8	98.6
0°-90°	656.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	656.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1123	
5°	1093	101
15°	825	227
25°	420	192
35°	141	92
45°	33	28
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1283500

CATALOG NUMBER: P3AS09R45B2750DE010 E3DL1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1123.4
2.5°	1116.4
5°	1092.9
7.5°	1052.5
10°	993.2
12.5°	914.6
15°	825.4
17.5°	726.3
20°	623.0
22.5°	518.0
25°	420.0
27.5°	330.9
30°	252.8
32.5°	190.1
35°	140.8
37.5°	103.8
40°	74.5
42.5°	51.6
45°	33.4
47.5°	18.8
50°	10.6
52.5°	8.2
55°	7.6
57.5°	7.0
60°	6.5
62.5°	5.9
65°	5.3
67.5°	4.7
70°	4.1
72.5°	3.5
75°	2.9
77.5°	2.3
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)