

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283502

Luminaire Tested: P3AS09R45B2750DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45B2750DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 249.0 lumens
Efficiency: N/A
Efficacy: 19.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283502

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1283502

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52803
5°	51860
10°	49075
15°	44745
20°	39577
25°	34357
30°	29498
35°	24574
40°	18320
45°	11226
50°	5185
55°	4052
60°	3903
65°	3580
70°	3334
75°	3135
80°	2904
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11226 cd/sqm

TEST NUMBER: P1283502

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.0	8.8
10°-20°	54.9	22.0
20°-30°	65.2	26.2
30°-40°	56.7	22.8
40°-50°	28.4	11.4
50°-60°	9.9	4.0
60°-70°	6.9	2.8
70°-80°	3.9	1.6
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	142.1	57.1
0°-40°	198.8	79.8
0°-60°	237.1	95.2
0°-90°	249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	249.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	241	
5°	236	22
15°	197	55
25°	142	65
35°	92	57
45°	36	28
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283502

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	240.8
2.5°	239.6
5°	235.6
7.5°	229.3
10°	220.4
12.5°	209.5
15°	197.1
17.5°	183.4
20°	169.6
22.5°	155.5
25°	142.0
27.5°	129.1
30°	116.5
32.5°	104.5
35°	91.8
37.5°	78.3
40°	64.0
42.5°	49.9
45°	36.2
47.5°	23.8
50°	15.2
52.5°	11.8
55°	10.6
57.5°	9.8
60°	8.9
62.5°	8.0
65°	6.9
67.5°	6.0
70°	5.2
72.5°	4.3
75°	3.7
77.5°	2.9
80°	2.3
82.5°	1.7
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)