

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284630

Luminaire Tested: P3AS13R25B2750DE010 E3DL1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284630
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25B2750DE010 E3DL1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 805.0 lumens
Efficiency: N/A
Efficacy: 42.1 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284630

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284630

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	516384
5°	481773
10°	385943
15°	261977
20°	158517
25°	92691
30°	52793
35°	29045
40°	15429
45°	8125
50°	4708
55°	3517
60°	3026
65°	3217
70°	2949
75°	2626
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8125 cd/sqm

TEST NUMBER: P1284630

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.2	24.1
10°-20°	317.3	39.4
20°-30°	181.3	22.5
30°-40°	71.5	8.9
40°-50°	21.9	2.7
50°-60°	8.7	1.1
60°-70°	5.8	0.7
70°-80°	3.2	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	692.8	86.1
0°-40°	764.3	94.9
0°-60°	794.9	98.7
0°-90°	805.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	805.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2355	
5°	2189	194
15°	1154	317
25°	383	181
35°	108	72
45°	26	22
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1284630

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2354.9
1°	2350.3
2°	2331.0
3°	2297.2
4°	2250.2
5°	2188.7
6°	2116.4
7°	2034.8
8°	1940.2
9°	1843.3
10°	1733.3
11°	1624.8
12°	1505.5
13°	1387.8
14°	1267.1
15°	1154.0
17.5°	894.7
20°	679.3
22.5°	510.1
25°	383.1
27.5°	283.9
30°	208.5
32.5°	150.8
35°	108.5
37.5°	76.9
40°	53.9
42.5°	36.9
45°	26.2
47.5°	18.5
50°	13.8
52.5°	10.8
55°	9.2
57.5°	8.5
60°	6.9
62.5°	6.2
65°	6.2
67.5°	5.4
70°	4.6
72.5°	3.8
75°	3.1
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1284630

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)