

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283535

Luminaire Tested: P3AS09R45B2750DE010 E3DLP1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283535
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45B2750DE010 E3DLP1GPH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 207.0 lumens
Efficiency: N/A
Efficacy: 15.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283535
CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1GPH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283535
 CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	94	94	94	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	86	83	81	79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	81	78	75	74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	73	69	66	64
7	83	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	69	65	61	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	65	61	58	56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	62	58	55	53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61662
5°	60246
10°	55577
15°	48332
20°	39693
25°	30897
30°	22814
35°	16062
40°	10019
45°	5427
50°	2934
55°	2523
60°	2281
65°	1920
70°	1667
75°	1694
80°	1389
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5427 cd/sqm



TEST NUMBER: P1283535
 CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.3	12.2
10°-20°	58.9	28.4
20°-30°	58.4	28.2
30°-40°	37.6	18.2
40°-50°	14.5	7.0
50°-60°	5.9	2.8
60°-70°	3.7	1.8
70°-80°	2.0	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	142.6	68.9
0°-40°	180.3	87.1
0°-60°	200.7	96.9
0°-90°	207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	281	
5°	274	25
15°	213	59
25°	128	58
35°	60	38
45°	18	14
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1283535
CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	281.2
2.5°	279.7
5°	273.7
7.5°	263.4
10°	249.6
12.5°	232.4
15°	212.9
17.5°	191.7
20°	170.1
22.5°	148.3
25°	127.7
27.5°	108.2
30°	90.1
32.5°	74.3
35°	60.0
37.5°	47.1
40°	35.0
42.5°	25.2
45°	17.5
47.5°	11.8
50°	8.6
52.5°	7.2
55°	6.6
57.5°	5.7
60°	5.2
62.5°	4.3
65°	3.7
67.5°	3.2
70°	2.6
72.5°	2.3
75°	2.0
77.5°	1.4
80°	1.1
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)