

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284631

Luminaire Tested: P3AS13R25B2750DE010 E3DL1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25B2750DE010 E3DL1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 860.0 lumens
Efficiency: N/A
Efficacy: 45.0 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284631

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284631

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95	94	93	92	91	90	89	88
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93	92	91	90	89	88	87	86	85	84
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	89	88	87	86	85	84	83	82	81	80	79
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	85	84	83	82	81	80	79	78	77	76	75
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	81	80	79	78	77	76	75	74	73	72	71
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	77	76	75	74	73	72	71	70	69	68	67
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	74	73	72	71	70	69	68	67	66	65	64
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	71	70	69	68	67	66	65	64	63	62	61
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	68	67	66	65	64	63	62	61	60	59	58
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	65	64	63	62	61	60	59	58	57	56	55
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	63	62	61	60	59	58	57	56	55	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	551666
5°	514681
10°	412306
15°	279865
20°	169345
25°	99030
30°	56388
35°	31026
40°	16459
45°	8652
50°	5049
55°	3785
60°	3245
65°	3424
70°	3142
75°	2796
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8652 cd/sqm

TEST NUMBER: P1284631

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.5	24.1
10°-20°	338.9	39.4
20°-30°	193.7	22.5
30°-40°	76.4	8.9
40°-50°	23.4	2.7
50°-60°	9.3	1.1
60°-70°	6.2	0.7
70°-80°	3.5	0.4
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.1	86.1
0°-40°	816.5	94.9
0°-60°	849.2	98.7
0°-90°	860.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	860.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2516	
5°	2338	207
15°	1233	339
25°	409	194
35°	116	76
45°	28	23
55°	10	9
65°	7	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1284631

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2515.8
1°	2510.8
2°	2490.3
3°	2454.1
4°	2404.0
5°	2338.2
6°	2261.0
7°	2173.9
8°	2072.8
9°	1969.2
10°	1851.7
11°	1735.8
12°	1608.4
13°	1482.7
14°	1353.6
15°	1232.8
17.5°	955.8
20°	725.7
22.5°	544.9
25°	409.3
27.5°	303.3
30°	222.7
32.5°	161.1
35°	115.9
37.5°	82.2
40°	57.5
42.5°	39.5
45°	27.9
47.5°	19.7
50°	14.8
52.5°	11.5
55°	9.9
57.5°	9.0
60°	7.4
62.5°	6.6
65°	6.6
67.5°	5.8
70°	4.9
72.5°	4.1
75°	3.3
77.5°	2.5
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.8



TEST NUMBER: P1284631

CATALOG NUMBER: P3AS13R25B2750DE010 E3DL1MW_5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)