

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283551

Luminaire Tested: P3AS09R45B2750DE010 E3DLP1MW\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1283551  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45B2750DE010 E3DLP1MW\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 80CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 452.0 lumens  
Efficiency: N/A  
Efficacy: 34.5 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1283551

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1283551

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 102 | 95  | 90  | 85  | 100 | 93  | 89  | 85  | 91  | 87  | 83  |  | 88  | 85  | 82  |  | 86  |
| 4   | 96  | 88  | 83  | 78  | 94  | 87  | 82  | 78  | 85  | 81  | 77  |  | 83  | 79  | 76  |  | 81  |
| 5   | 91  | 83  | 77  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  |  | 78  | 74  | 71  |  | 77  |
| 6   | 87  | 78  | 72  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  |  | 74  | 69  | 66  |  | 73  |
| 7   | 83  | 73  | 67  | 63  | 81  | 72  | 67  | 63  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  |
| 8   | 79  | 69  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 58  |  | 66  | 62  | 58  |  | 65  |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 59  | 55  |  | 63  | 58  | 55  |  | 62  |
| 10  | 72  | 62  | 56  | 52  | 71  | 61  | 56  | 52  | 61  | 55  | 52  |  | 60  | 55  | 52  |  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 134638 |
| 5°  | 131565 |
| 10° | 121374 |
| 15° | 105540 |
| 20° | 86691  |
| 25° | 67456  |
| 30° | 49805  |
| 35° | 35041  |
| 40° | 21870  |
| 45° | 11846  |
| 50° | 6413   |
| 55° | 5505   |
| 60° | 4956   |
| 65° | 4203   |
| 70° | 3590   |
| 75° | 3728   |
| 80° | 3157   |
| 85° | 3271   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11846 cd/sqm

TEST NUMBER: P1283551

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1MW\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 55.4   | 12.2      |
| 10°-20°   | 128.5  | 28.4      |
| 20°-30°   | 127.6  | 28.2      |
| 30°-40°   | 82.2   | 18.2      |
| 40°-50°   | 31.6   | 7.0       |
| 50°-60°   | 12.9   | 2.8       |
| 60°-70°   | 8.1    | 1.8       |
| 70°-80°   | 4.4    | 1.0       |
| 80°-90°   | 1.4    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 311.4  | 68.9      |
| 0°-40°    | 393.6  | 87.1      |
| 0°-60°    | 438.1  | 96.9      |
| 0°-90°    | 452.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 452.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 614 |      |
| 5°  | 598 | 55   |
| 15° | 465 | 129  |
| 25° | 279 | 128  |
| 35° | 131 | 82   |
| 45° | 38  | 32   |
| 55° | 14  | 13   |
| 65° | 8   | 8    |
| 75° | 4   | 4    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1283551

CATALOG NUMBER: P3AS09R45B2750DE010 E3DLP1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 614.0 |
| 2.5°  | 610.8 |
| 5°    | 597.7 |
| 7.5°  | 575.1 |
| 10°   | 545.1 |
| 12.5° | 507.5 |
| 15°   | 464.9 |
| 17.5° | 418.5 |
| 20°   | 371.5 |
| 22.5° | 323.9 |
| 25°   | 278.8 |
| 27.5° | 236.2 |
| 30°   | 196.7 |
| 32.5° | 162.3 |
| 35°   | 130.9 |
| 37.5° | 102.7 |
| 40°   | 76.4  |
| 42.5° | 55.1  |
| 45°   | 38.2  |
| 47.5° | 25.7  |
| 50°   | 18.8  |
| 52.5° | 15.7  |
| 55°   | 14.4  |
| 57.5° | 12.5  |
| 60°   | 11.3  |
| 62.5° | 9.4   |
| 65°   | 8.1   |
| 67.5° | 6.9   |
| 70°   | 5.6   |
| 72.5° | 5.0   |
| 75°   | 4.4   |
| 77.5° | 3.1   |
| 80°   | 2.5   |
| 82.5° | 1.9   |
| 85°   | 1.3   |
| 87.5° | 0.6   |
| 90°   | 0.0   |

(END OF REPORT)