

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283576

Luminaire Tested: P3AS09R50B2750DE010 E3CB1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50B2750DE010 E3CB1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 80CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 858.0 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283576
CATALOG NUMBER: P3AS09R50B2750DE010 E3CB1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283576
 CATALOG NUMBER: P3AS09R50B2750DE010 E3CB1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95				95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90				90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80				80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76				76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72				72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65				65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62				62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59				59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	298814
5°	293462
10°	281781
15°	258390
20°	227846
25°	174639
30°	94951
35°	30544
40°	7185
45°	961
50°	853
55°	956
60°	833
65°	986
70°	833
75°	1101
80°	758
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 85°
 Luminance: 1510 cd/sqm



TEST NUMBER: P1283576
 CATALOG NUMBER: P3AS09R50B2750DE010 E3CB1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	14.6
10°-20°	316.4	36.9
20°-30°	316.9	36.9
30°-40°	89.1	10.4
40°-50°	5.4	0.6
50°-60°	2.0	0.2
60°-70°	1.7	0.2
70°-80°	1.1	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	758.4	88.4
0°-40°	847.4	98.8
0°-60°	854.8	99.6
0°-90°	858.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	858.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1363	
5°	1333	125
15°	1138	316
25°	722	317
35°	114	89
45°	3	5
55°	2	2
65°	2	2
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P1283576
CATALOG NUMBER: P3AS09R50B2750DE010 E3CB1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1362.7
2.5°	1355.8
5°	1333.2
7.5°	1302.5
10°	1265.5
12.5°	1209.7
15°	1138.2
17.5°	1056.1
20°	976.4
22.5°	877.3
25°	721.8
27.5°	537.4
30°	375.0
32.5°	226.4
35°	114.1
37.5°	53.9
40°	25.1
42.5°	9.4
45°	3.1
47.5°	2.5
50°	2.5
52.5°	2.5
55°	2.5
57.5°	1.9
60°	1.9
62.5°	1.9
65°	1.9
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)