

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284644

Luminaire Tested: P3AS13R25B2750DE010 E3DLD1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25B2750DE010 E3DLD1GPH_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 80CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 305.0 lumens
Efficiency: N/A
Efficacy: 16.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284644

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1284644

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72494
5°	70768
10°	65574
15°	58389
20°	50194
25°	42656
30°	35119
35°	27358
40°	19694
45°	12497
50°	7403
55°	5085
60°	4649
65°	4358
70°	3911
75°	3558
80°	3410
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 12497 cd/sqm

TEST NUMBER: P1284644

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.8	9.8
10°-20°	71.4	23.4
20°-30°	80.7	26.5
30°-40°	63.8	20.9
40°-50°	32.3	10.6
50°-60°	12.9	4.2
60°-70°	8.3	2.7
70°-80°	4.6	1.5
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.9	59.6
0°-40°	245.7	80.6
0°-60°	290.9	95.4
0°-90°	305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	305.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	331	
5°	322	30
15°	257	71
25°	176	81
35°	102	64
45°	40	32
55°	13	13
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1284644

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	330.6
1°	330.6
2°	329.4
3°	327.5
4°	324.9
5°	321.5
6°	317.3
7°	312.3
8°	307.0
9°	300.9
10°	294.5
11°	287.3
12°	280.4
13°	272.4
14°	264.8
15°	257.2
17.5°	236.0
20°	215.1
22.5°	195.3
25°	176.3
27.5°	157.7
30°	138.7
32.5°	120.8
35°	102.2
37.5°	85.1
40°	68.8
42.5°	53.6
45°	40.3
47.5°	30.0
50°	21.7
52.5°	16.3
55°	13.3
57.5°	12.2
60°	10.6
62.5°	9.5
65°	8.4
67.5°	7.2
70°	6.1
72.5°	5.3
75°	4.2
77.5°	3.4
80°	2.7
82.5°	1.9
85°	1.1
87.5°	0.4



TEST NUMBER: P1284644

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)