

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284667

Luminaire Tested: P3AS13R25B2750DE010 E3DLD1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1284667  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25B2750DE010 E3DLD1WMH\_2700K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 616.0 lumens  
Efficiency: N/A  
Efficacy: 32.3 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1284667  
CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1284667

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	146392
5°	142901
10°	132418
15°	117935
20°	101369
25°	86158
30°	70922
35°	55252
40°	39760
45°	25212
50°	14908
55°	10284
60°	9429
65°	8769
70°	7886
75°	7117
80°	6819
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25212 cd/sqm



TEST NUMBER: P1284667

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.2	9.8
10°-20°	144.2	23.4
20°-30°	163.0	26.5
30°-40°	128.9	20.9
40°-50°	65.1	10.6
50°-60°	26.1	4.2
60°-70°	16.7	2.7
70°-80°	9.2	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	367.4	59.6
0°-40°	496.3	80.6
0°-60°	587.5	95.4
0°-90°	616.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	616.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	668	
5°	649	60
15°	520	144
25°	356	163
35°	206	129
45°	81	65
55°	27	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1284667

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	667.6
1°	667.6
2°	665.3
3°	661.5
4°	656.1
5°	649.2
6°	640.8
7°	630.8
8°	620.1
9°	607.8
10°	594.7
11°	580.2
12°	566.3
13°	550.2
14°	534.9
15°	519.5
17.5°	476.6
20°	434.4
22.5°	394.4
25°	356.1
27.5°	318.5
30°	280.1
32.5°	244.0
35°	206.4
37.5°	171.9
40°	138.9
42.5°	108.2
45°	81.3
47.5°	60.6
50°	43.7
52.5°	33.0
55°	26.9
57.5°	24.6
60°	21.5
62.5°	19.2
65°	16.9
67.5°	14.6
70°	12.3
72.5°	10.7
75°	8.4
77.5°	6.9
80°	5.4
82.5°	3.8
85°	2.3
87.5°	0.8



TEST NUMBER: P1284667  
CATALOG NUMBER: P3AS13R25B2750DE010 E3DLD1WMH\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)