

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284672

Luminaire Tested: P3AS13R25B2750DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25B2750DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 241.0 lumens
Efficiency: N/A
Efficacy: 12.6 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284672

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1284672

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		64	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87493
5°	83953
10°	73546
15°	59115
20°	45411
25°	34357
30°	24839
35°	16490
40°	9990
45°	5830
50°	3718
55°	3020
60°	2631
65°	2335
70°	1923
75°	1949
80°	1389
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5830 cd/sqm

TEST NUMBER: P1284672

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.7	14.4
10°-20°	72.0	29.9
20°-30°	65.1	27.0
30°-40°	39.1	16.2
40°-50°	15.5	6.4
50°-60°	7.2	3.0
60°-70°	4.4	1.8
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	171.8	71.3
0°-40°	210.9	87.5
0°-60°	233.6	96.9
0°-90°	241.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	241.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	399	
5°	381	35
15°	260	72
25°	142	65
35°	62	39
45°	19	16
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1284672

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	399.0
1°	399.0
2°	397.1
3°	393.0
4°	387.7
5°	381.4
6°	373.1
7°	363.7
8°	352.8
9°	341.9
10°	330.3
11°	316.7
12°	302.8
13°	288.9
14°	275.0
15°	260.4
17.5°	225.8
20°	194.6
22.5°	166.4
25°	142.0
27.5°	119.1
30°	98.1
32.5°	78.9
35°	61.6
37.5°	47.0
40°	34.9
42.5°	25.5
45°	18.8
47.5°	14.3
50°	10.9
52.5°	9.0
55°	7.9
57.5°	6.8
60°	6.0
62.5°	4.9
65°	4.5
67.5°	3.8
70°	3.0
72.5°	2.6
75°	2.3
77.5°	1.9
80°	1.1
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1284672

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)