

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283635

Luminaire Tested: P3AS09R50B2750DE010 E3DL1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50B2750DE010 E3DL1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 80CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 660.0 lumens
Efficiency: N/A
Efficacy: 50.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283635

CATALOG NUMBER: P3AS09R50B2750DE010 E3DL1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283635

CATALOG NUMBER: P3AS09R50B2750DE010 E3DL1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67		
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64		
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60		
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57		
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210137
5°	205899
10°	192849
15°	172646
20°	145286
25°	110885
30°	72062
35°	42724
40°	24703
45°	12373
50°	4605
55°	3594
60°	3333
65°	3061
70°	3013
75°	2965
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12373 cd/sqm

TEST NUMBER: P1283635

CATALOG NUMBER: P3AS09R50B2750DE010 E3DL1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	13.2
10°-20°	210.3	31.9
20°-30°	206.3	31.3
30°-40°	104.0	15.8
40°-50°	32.8	5.0
50°-60°	8.5	1.3
60°-70°	6.0	0.9
70°-80°	3.7	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	503.7	76.3
0°-40°	607.6	92.1
0°-60°	649.0	98.3
0°-90°	660.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	660.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	958	
5°	935	87
15°	760	210
25°	458	206
35°	160	104
45°	40	33
55°	9	9
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283635

CATALOG NUMBER: P3AS09R50B2750DE010 E3DL1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	958.3
2.5°	952.4
5°	935.4
7.5°	904.9
10°	866.1
12.5°	816.3
15°	760.5
17.5°	696.0
20°	622.6
22.5°	543.4
25°	458.3
27.5°	367.9
30°	284.6
32.5°	214.2
35°	159.6
37.5°	118.0
40°	86.3
42.5°	61.0
45°	39.9
47.5°	22.9
50°	13.5
52.5°	10.0
55°	9.4
57.5°	8.2
60°	7.6
62.5°	7.0
65°	5.9
67.5°	5.3
70°	4.7
72.5°	4.1
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)