

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283695

Luminaire Tested: P3AS09R50B2750DE010 E3DLP1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283695
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50B2750DE010 E3DLP1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 80CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 433.0 lumens
Efficiency: N/A
Efficacy: 33.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283695

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283695

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68		
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60		
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56		
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125933
5°	122540
10°	113002
15°	99388
20°	83144
25°	65931
30°	48362
35°	33247
40°	21125
45°	11815
50°	6413
55°	5390
60°	4605
65°	4255
70°	3783
75°	3474
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11815 cd/sqm

TEST NUMBER: P1283695

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	11.9
10°-20°	121.2	28.0
20°-30°	124.0	28.6
30°-40°	78.6	18.2
40°-50°	31.3	7.2
50°-60°	12.7	2.9
60°-70°	8.1	1.9
70°-80°	4.2	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.8	68.6
0°-40°	375.4	86.7
0°-60°	419.4	96.9
0°-90°	433.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	433.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	574	
5°	557	52
15°	438	121
25°	272	124
35°	124	79
45°	38	31
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283695

CATALOG NUMBER: P3AS09R50B2750DE010 E3DLP1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	574.3
2.5°	570.2
5°	556.7
7.5°	535.6
10°	507.5
12.5°	474.1
15°	437.8
17.5°	397.9
20°	356.3
22.5°	314.7
25°	272.5
27.5°	230.3
30°	191.0
32.5°	155.9
35°	124.2
37.5°	97.3
40°	73.8
42.5°	54.5
45°	38.1
47.5°	25.8
50°	18.8
52.5°	15.8
55°	14.1
57.5°	12.3
60°	10.5
62.5°	9.4
65°	8.2
67.5°	7.0
70°	5.9
72.5°	4.7
75°	4.1
77.5°	2.9
80°	2.3
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)