

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283763

Luminaire Tested: P3AS09R55B2750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55B2750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 23.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283763

CATALOG NUMBER: P3AS09R55B2750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283763

CATALOG NUMBER: P3AS09R55B2750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84577
5°	83711
10°	80849
15°	74734
20°	64476
25°	50930
30°	36132
35°	23289
40°	13998
45°	7877
50°	4230
55°	1529
60°	1360
65°	1297
70°	1282
75°	1186
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7877 cd/sqm

TEST NUMBER: P1283763

CATALOG NUMBER: P3AS09R55B2750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.8	11.6
10°-20°	91.0	29.6
20°-30°	95.4	31.0
30°-40°	55.6	18.1
40°-50°	20.8	6.8
50°-60°	4.9	1.6
60°-70°	2.5	0.8
70°-80°	1.5	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.2	72.1
0°-40°	277.8	90.2
0°-60°	303.6	98.6
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	386	
5°	380	36
15°	329	91
25°	210	95
35°	87	56
45°	25	21
55°	4	5
65°	2	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1283763

CATALOG NUMBER: P3AS09R55B2750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	385.7
2.5°	384.6
5°	380.3
7.5°	373.5
10°	363.1
12.5°	348.4
15°	329.2
17.5°	304.9
20°	276.3
22.5°	244.4
25°	210.5
27.5°	175.8
30°	142.7
32.5°	112.7
35°	87.0
37.5°	66.1
40°	48.9
42.5°	35.0
45°	25.4
47.5°	18.4
50°	12.4
52.5°	7.1
55°	4.0
57.5°	3.4
60°	3.1
62.5°	2.8
65°	2.5
67.5°	2.3
70°	2.0
72.5°	1.7
75°	1.4
77.5°	1.1
80°	0.8
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)