

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284762

Luminaire Tested: P3AS13R30B2750DE010 E3D1WH_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30B2750DE010 E3D1WH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 969.0 lumens
Efficiency: N/A
Efficacy: 50.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284762

CATALOG NUMBER: P3AS13R30B2750DE010 E3D1WH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1284762

CATALOG NUMBER: P3AS13R30B2750DE010 E3D1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	96	95	94	93	92	91	90	89
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87	86
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	91	90	89	88	87	86	85	84	83	82	81	80
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	87	86	85	84	83	82	81	80	79	78	77
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83	82	81	80	79	78	77	76	75	74
6	99	92	88	85	97	92	88	85	90	87	84	89	86	84	88	85	83	82	81	80	79	78	77	76	75	74	73	72	71
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78	77	76	75	74	73	72	71	70	69
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76	75	74	73	72	71	70	69	68	67
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74	73	72	71	70	69	68	67	66	65
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72	71	70	69	68	67	66	65	64	63

AVERAGE LUMINANCE (cd/sqm):

0°	770969
5°	760905
10°	664339
15°	422273
20°	167291
25°	55890
30°	26004
35°	11778
40°	4523
45°	2202
50°	648
55°	306
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2202 cd/sqm

TEST NUMBER: P1284762

CATALOG NUMBER: P3AS13R30B2750DE010 E3D1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	316.0	32.6
10°-20°	490.1	50.6
20°-30°	126.4	13.0
30°-40°	29.7	3.1
40°-50°	5.8	0.6
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	932.5	96.2
0°-40°	962.2	99.3
0°-60°	968.7	100.0
0°-90°	969.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3516	
5°	3457	316
15°	1860	490
25°	231	126
35°	44	30
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1284762

CATALOG NUMBER: P3AS13R30B2750DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3515.9
1°	3513.3
2°	3505.0
3°	3495.6
4°	3481.7
5°	3456.8
6°	3416.6
7°	3349.6
8°	3258.2
9°	3139.0
10°	2983.6
11°	2798.9
12°	2597.3
13°	2365.2
14°	2122.2
15°	1860.1
16°	1603.2
17°	1355.6
18°	1118.3
19°	900.5
20°	716.9
21°	564.2
22°	443.9
23°	351.3
24°	281.4
25°	231.0
26°	192.6
27°	163.6
28°	141.4
29°	121.1
30°	102.7
32.5°	64.7
35°	44.0
37.5°	27.5
40°	15.8
42.5°	10.5
45°	7.1
47.5°	4.1
50°	1.9
52.5°	0.8
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P1284762

CATALOG NUMBER: P3AS13R30B2750DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)