

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283848

Luminaire Tested: P3AS09R55B2750DE010 E3DLP1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283848
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55B2750DE010 E3DLP1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 420.0 lumens
Efficiency: N/A
Efficacy: 32.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283848

CATALOG NUMBER: P3AS09R55B2750DE010 E3DLP1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1283848

CATALOG NUMBER: P3AS09R55B2750DE010 E3DLP1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94		92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87		85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	83	80		79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80	77	74		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69		67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	68	64		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68	63	60		59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56		55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53		52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58	53	50		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114245
5°	111380
10°	103561
15°	92214
20°	78360
25°	63246
30°	48210
35°	34291
40°	22614
45°	13428
50°	7880
55°	4855
60°	4298
65°	3891
70°	3334
75°	2965
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13428 cd/sqm

TEST NUMBER: P1283848

CATALOG NUMBER: P3AS09R55B2750DE010 E3DLP1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	11.2
10°-20°	112.6	26.8
20°-30°	119.3	28.4
30°-40°	80.6	19.2
40°-50°	35.3	8.4
50°-60°	12.6	3.0
60°-70°	7.4	1.8
70°-80°	3.9	0.9
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.9	66.4
0°-40°	359.5	85.6
0°-60°	407.4	97.0
0°-90°	420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	420.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	521	
5°	506	47
15°	406	113
25°	261	119
35°	128	81
45°	43	35
55°	13	13
65°	8	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1283848

CATALOG NUMBER: P3AS09R55B2750DE010 E3DLP1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	521.0
2.5°	517.0
5°	506.0
7.5°	488.1
10°	465.1
12.5°	437.4
15°	406.2
17.5°	371.6
20°	335.8
22.5°	298.3
25°	261.4
27.5°	225.0
30°	190.4
32.5°	157.5
35°	128.1
37.5°	101.6
40°	79.0
42.5°	59.4
45°	43.3
47.5°	31.7
50°	23.1
52.5°	16.2
55°	12.7
57.5°	11.5
60°	9.8
62.5°	8.7
65°	7.5
67.5°	6.3
70°	5.2
72.5°	4.6
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)