

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284828

Luminaire Tested: P3AS13R30B2750DE010 E3DLD1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30B2750DE010 E3DLD1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 616.0 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284828
CATALOG NUMBER: P3AS13R30B2750DE010 E3DLD1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284828

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLD1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	9.7
10°-20°	144.1	23.4
20°-30°	162.5	26.4
30°-40°	129.7	21.1
40°-50°	66.7	10.8
50°-60°	25.1	4.1
60°-70°	16.5	2.7
70°-80°	8.9	1.4
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.6	59.5
0°-40°	496.3	80.6
0°-60°	588.1	95.5
0°-90°	616.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	616.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	664	
5°	646	60
15°	518	144
25°	354	162
35°	209	130
45°	85	67
55°	26	25
65°	17	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1284828
CATALOG NUMBER: P3AS13R30B2750DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	663.7
1°	663.7
2°	661.4
3°	657.6
4°	652.3
5°	646.3
6°	638.7
7°	628.9
8°	618.3
9°	606.2
10°	594.1
11°	580.5
12°	566.2
13°	551.0
14°	535.2
15°	518.5
17.5°	476.2
20°	433.9
22.5°	393.1
25°	354.5
27.5°	316.7
30°	281.2
32.5°	244.9
35°	208.6
37.5°	173.1
40°	139.8
42.5°	110.4
45°	84.7
47.5°	62.7
50°	43.8
52.5°	31.0
55°	25.7
57.5°	23.4
60°	21.2
62.5°	18.9
65°	16.6
67.5°	14.4
70°	12.1
72.5°	9.8
75°	8.3
77.5°	6.8
80°	5.3
82.5°	3.8
85°	2.3
87.5°	0.8



TEST NUMBER: P1284828
CATALOG NUMBER: P3AS13R30B2750DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)