

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284865

Luminaire Tested: P3AS13R30B2750DE010 E3PH1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30B2750DE010 E3PH1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 80CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 792.0 lumens
Efficiency: N/A
Efficacy: 41.5 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284865

CATALOG NUMBER: P3AS13R30B2750DE010 E3PH1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284865

CATALOG NUMBER: P3AS13R30B2750DE010 E3PH1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93
4	106	101	98	95	105	100	97	95	98	96	94	97	94	92	95	93	91	90	90	90
5	104	98	95	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88	88	88
6	101	95	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87	86	86	86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84	84	84
8	96	91	87	84	96	90	87	84	89	86	84	88	86	84	88	85	83	83	83	83
9	94	89	85	82	94	88	85	82	87	84	82	87	84	82	86	84	82	81	81	81
10	92	87	83	81	92	86	83	81	86	82	80	85	82	80	84	82	80	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1127300
5°	984721
10°	540204
15°	248537
20°	133968
25°	45390
30°	5900
35°	883
40°	315
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1284865

CATALOG NUMBER: P3AS13R30B2750DE010 E3PH1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.4	45.3
10°-20°	328.5	41.5
20°-30°	101.0	12.8
30°-40°	3.8	0.5
40°-50°	0.3	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.9	99.5
0°-40°	791.7	100.0
0°-60°	792.0	100.0
0°-90°	792.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	792.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5141	
5°	4474	358
15°	1095	328
25°	188	101
35°	3	4
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1284865

CATALOG NUMBER: P3AS13R30B2750DE010 E3PH1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5140.9
2.5°	5021.0
5°	4473.6
7.5°	3509.8
10°	2426.1
12.5°	1642.2
15°	1094.8
17.5°	767.3
20°	574.1
22.5°	386.4
25°	187.6
27.5°	68.8
30°	23.3
32.5°	7.8
35°	3.3
37.5°	2.2
40°	1.1
42.5°	1.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)