

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284886

Luminaire Tested: P3AS13R35B2750DE010 E3CB1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284886
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35B2750DE010 E3CB1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 80CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1043.0 lumens
Efficiency: N/A
Efficacy: 54.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284886

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MMS_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284886

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	98	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	680099
5°	666254
10°	619828
15°	454418
20°	232700
25°	83860
30°	32663
35°	11430
40°	4695
45°	1271
50°	1126
55°	1262
60°	1096
65°	830
70°	1026
75°	1356
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 75°
Luminance: 1356 cd/sqm

TEST NUMBER: P1284886

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.2	27.1
10°-20°	529.4	50.8
20°-30°	187.4	18.0
30°-40°	32.8	3.1
40°-50°	4.8	0.5
50°-60°	2.7	0.3
60°-70°	1.9	0.2
70°-80°	1.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	999.0	95.8
0°-40°	1031.9	98.9
0°-60°	1039.3	99.7
0°-90°	1043.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1043.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3102	
5°	3027	282
15°	2002	529
25°	347	187
35°	43	33
45°	4	5
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1284886

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3101.5
1°	3100.7
2°	3090.8
3°	3072.0
4°	3054.7
5°	3026.8
6°	2998.0
7°	2966.0
8°	2926.6
9°	2865.0
10°	2783.7
11°	2671.1
12°	2535.6
13°	2374.6
14°	2197.2
15°	2001.7
17.5°	1490.8
20°	997.2
22.5°	601.2
25°	346.6
27.5°	207.0
30°	129.0
32.5°	74.7
35°	42.7
37.5°	27.1
40°	16.4
42.5°	8.2
45°	4.1
47.5°	3.3
50°	3.3
52.5°	3.3
55°	3.3
57.5°	2.5
60°	2.5
62.5°	2.5
65°	1.6
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0



TEST NUMBER: P1284886

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MMS_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)