

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284888

Luminaire Tested: P3AS13R35B2750DE010 E3CB1MW\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1284888  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R35B2750DE010 E3CB1MW\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 960.0 lumens  
Efficiency: N/A  
Efficacy: 50.3 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1284888  
CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1284888

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	94	94	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	94	92	90	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	84	81	79	77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	81	78	76	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	77	74	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	625981
5°	613228
10°	570486
15°	418254
20°	214172
25°	77182
30°	30055
35°	10520
40°	4322
45°	1178
50°	1023
55°	1147
60°	1009
65°	778
70°	962
75°	1271
80°	1010
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 1344 cd/sqm



TEST NUMBER: P1284888

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	259.7	27.1
10°-20°	487.3	50.8
20°-30°	172.5	18.0
30°-40°	30.2	3.1
40°-50°	4.4	0.5
50°-60°	2.4	0.3
60°-70°	1.8	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	919.5	95.8
0°-40°	949.7	98.9
0°-60°	956.6	99.6
0°-90°	960.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	960.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2855	
5°	2786	260
15°	1842	487
25°	319	173
35°	39	30
45°	4	4
55°	3	2
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1284888  
CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2854.7
1°	2854.0
2°	2844.9
3°	2827.5
4°	2811.6
5°	2785.9
6°	2759.5
7°	2730.0
8°	2693.7
9°	2637.0
10°	2562.1
11°	2458.6
12°	2333.8
13°	2185.6
14°	2022.3
15°	1842.4
17.5°	1372.2
20°	917.8
22.5°	553.4
25°	319.0
27.5°	190.5
30°	118.7
32.5°	68.8
35°	39.3
37.5°	24.9
40°	15.1
42.5°	7.6
45°	3.8
47.5°	3.0
50°	3.0
52.5°	3.0
55°	3.0
57.5°	2.3
60°	2.3
62.5°	2.3
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0



TEST NUMBER: P1284888  
CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)