

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284938

Luminaire Tested: P3AS13R35B2750DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35B2750DE010 E3DL1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 795.0 lumens
Efficiency: N/A
Efficacy: 41.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284938
CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284938
 CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	400955
5°	385339
10°	335754
15°	257164
20°	172052
25°	104111
30°	59731
35°	33408
40°	17748
45°	9148
50°	4401
55°	3479
60°	3333
65°	2750
70°	2885
75°	2542
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9148 cd/sqm



TEST NUMBER: P1284938

CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.3	20.0
10°-20°	308.7	38.8
20°-30°	202.1	25.4
30°-40°	82.0	10.3
40°-50°	24.6	3.1
50°-60°	8.4	1.1
60°-70°	5.6	0.7
70°-80°	3.3	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.0	84.3
0°-40°	752.0	94.6
0°-60°	785.0	98.7
0°-90°	795.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	795.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1828	
5°	1751	159
15°	1133	309
25°	430	202
35°	125	82
45°	30	25
55°	9	8
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1284938
CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1828.5
1°	1825.5
2°	1817.2
3°	1800.6
4°	1780.9
5°	1750.6
6°	1712.8
7°	1670.5
8°	1622.8
9°	1568.4
10°	1507.9
11°	1440.6
12°	1370.3
13°	1291.6
14°	1216.8
15°	1132.8
17.5°	929.4
20°	737.3
22.5°	567.2
25°	430.3
27.5°	320.6
30°	235.9
32.5°	173.2
35°	124.8
37.5°	88.5
40°	62.0
42.5°	43.1
45°	29.5
47.5°	19.7
50°	12.9
52.5°	9.8
55°	9.1
57.5°	8.3
60°	7.6
62.5°	6.8
65°	5.3
67.5°	4.5
70°	4.5
72.5°	3.8
75°	3.0
77.5°	2.3
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1284938
CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)