

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284944

Luminaire Tested: P3AS13R35B2750DE010 E3DLD1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284944
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35B2750DE010 E3DLD1GPH_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3500K CCT AND, 80CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 16.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284944

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1284944

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70367
5°	68875
10°	64483
15°	57889
20°	50358
25°	42922
30°	35955
35°	28643
40°	20696
45°	13087
50°	7130
55°	4932
60°	4693
65°	4358
70°	4167
75°	3558
80°	3410
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13087 cd/sqm

TEST NUMBER: P1284944

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.1	9.5
10°-20°	71.0	23.0
20°-30°	81.3	26.4
30°-40°	66.4	21.6
40°-50°	33.4	10.9
50°-60°	12.4	4.0
60°-70°	8.3	2.7
70°-80°	4.6	1.5
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.4	58.9
0°-40°	247.8	80.5
0°-60°	293.6	95.3
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	321	
5°	313	29
15°	255	71
25°	177	81
35°	107	66
45°	42	33
55°	13	12
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1284944

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	320.9
1°	320.5
2°	319.7
3°	318.2
4°	315.9
5°	312.9
6°	309.1
7°	305.2
8°	300.3
9°	295.4
10°	289.6
11°	283.6
12°	277.1
13°	269.8
14°	262.2
15°	255.0
17.5°	235.6
20°	215.8
22.5°	195.6
25°	177.4
27.5°	159.5
30°	142.0
32.5°	124.5
35°	107.0
37.5°	89.4
40°	72.3
42.5°	56.3
45°	42.2
47.5°	30.4
50°	20.9
52.5°	15.2
55°	12.9
57.5°	11.8
60°	10.7
62.5°	9.5
65°	8.4
67.5°	7.2
70°	6.5
72.5°	5.3
75°	4.2
77.5°	3.4
80°	2.7
82.5°	1.9
85°	1.1
87.5°	0.8



TEST NUMBER: P1284944

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)