

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1283966

Luminaire Tested: P3AS09R60B2750DE010 E3DLD1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1283966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60B2750DE010 E3DLD1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 516.0 lumens
Efficiency: N/A
Efficacy: 39.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1283966

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1283966

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91594
5°	90579
10°	87440
15°	82611
20°	76143
25°	68956
30°	61199
35°	52307
40°	41592
45°	29336
50°	17535
55°	8869
60°	8508
65°	7783
70°	7245
75°	6863
80°	6314
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29336 cd/sqm

TEST NUMBER: P1283966

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	7.5
10°-20°	101.7	19.7
20°-30°	130.6	25.3
30°-40°	121.0	23.5
40°-50°	73.7	14.3
50°-60°	24.6	4.8
60°-70°	15.0	2.9
70°-80°	8.4	1.6
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.9	52.5
0°-40°	392.0	76.0
0°-60°	490.3	95.0
0°-90°	516.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	516.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	418	
5°	412	39
15°	364	102
25°	285	131
35°	195	121
45°	95	74
55°	23	25
65°	15	15
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1283966

CATALOG NUMBER: P3AS09R60B2750DE010 E3DLD1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	417.7
2.5°	415.8
5°	411.5
7.5°	403.3
10°	392.7
12.5°	379.5
15°	363.9
17.5°	345.7
20°	326.3
22.5°	305.6
25°	285.0
27.5°	263.7
30°	241.7
32.5°	219.8
35°	195.4
37.5°	169.7
40°	145.3
42.5°	119.6
45°	94.6
47.5°	73.3
50°	51.4
52.5°	30.7
55°	23.2
57.5°	21.3
60°	19.4
62.5°	16.9
65°	15.0
67.5°	13.2
70°	11.3
72.5°	9.4
75°	8.1
77.5°	6.3
80°	5.0
82.5°	3.1
85°	1.9
87.5°	1.3
90°	0.0

(END OF REPORT)