

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284954

Luminaire Tested: P3AS13R35B2750DE010 E3DLD1LI_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35B2750DE010 E3DLD1LI_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3500K CCT AND, 80CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 628.0 lumens
Efficiency: N/A
Efficacy: 32.9 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284954

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1LI_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1284954

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1LI_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89	87	85	83
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83	80	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78	74	71	69
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68	64	61	59
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64	60	56	55
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143453
5°	140413
10°	131505
15°	118026
20°	102676
25°	87489
30°	73302
35°	58384
40°	42193
45°	26700
50°	14567
55°	10093
60°	9517
65°	8873
70°	8463
75°	7202
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26700 cd/sqm

TEST NUMBER: P1284954

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1LI_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.4	9.5
10°-20°	144.7	23.0
20°-30°	165.8	26.4
30°-40°	135.3	21.5
40°-50°	68.2	10.9
50°-60°	25.3	4.0
60°-70°	17.0	2.7
70°-80°	9.4	1.5
80°-90°	2.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.9	58.9
0°-40°	505.2	80.4
0°-60°	598.8	95.3
0°-90°	628.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	628.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	654	
5°	638	59
15°	520	145
25°	362	166
35°	218	135
45°	86	68
55°	26	25
65°	17	17
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1284954

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1LI_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	654.2
1°	653.4
2°	651.9
3°	648.8
4°	644.1
5°	637.9
6°	630.1
7°	622.4
8°	612.3
9°	602.2
10°	590.6
11°	578.2
12°	565.0
13°	550.2
14°	534.7
15°	519.9
17.5°	480.4
20°	440.0
22.5°	398.9
25°	361.6
27.5°	325.2
30°	289.5
32.5°	253.8
35°	218.1
37.5°	182.4
40°	147.4
42.5°	114.9
45°	86.1
47.5°	62.1
50°	42.7
52.5°	31.0
55°	26.4
57.5°	24.1
60°	21.7
62.5°	19.4
65°	17.1
67.5°	14.7
70°	13.2
72.5°	10.9
75°	8.5
77.5°	7.0
80°	5.4
82.5°	3.9
85°	2.3
87.5°	1.6



TEST NUMBER: P1284954

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1LI_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)