

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284005

Luminaire Tested: P3AS09R65B2750DE010 E3CB1MMS_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284005
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65B2750DE010 E3CB1MMS_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 80CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 726.0 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284005

CATALOG NUMBER: P3AS09R65B2750DE010 E3CB1MMS_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284005

CATALOG NUMBER: P3AS09R65B2750DE010 E3CB1MMS_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	93		95	93	91		92	90	89
3	103	96	91	87		101	95	90	87		92	88	85		90	87	84		88	85	83
4	97	90	84	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	69	64	60		68	63	60		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		61	56	53		60	56	53		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177420
5°	166982
10°	164860
15°	161953
20°	152917
25°	141928
30°	110321
35°	63818
40°	25705
45°	11846
50°	4605
55°	1797
60°	1535
65°	1505
70°	1475
75°	1525
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11846 cd/sqm

TEST NUMBER: P1284005

CATALOG NUMBER: P3AS09R65B2750DE010 E3CB1MMS_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.1	9.9
10°-20°	199.2	27.4
20°-30°	260.8	35.9
30°-40°	151.1	20.8
40°-50°	32.3	4.5
50°-60°	5.3	0.7
60°-70°	2.9	0.4
70°-80°	1.7	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.1	73.3
0°-40°	683.2	94.1
0°-60°	720.8	99.3
0°-90°	726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	726.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	809	
5°	759	72
15°	713	199
25°	587	261
35°	238	151
45°	38	32
55°	5	5
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1284005

CATALOG NUMBER: P3AS09R65B2750DE010 E3CB1MMS_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	809.1
2.5°	786.2
5°	758.6
7.5°	747.4
10°	740.4
12.5°	730.4
15°	713.4
17.5°	687.0
20°	655.3
22.5°	625.3
25°	586.6
27.5°	521.4
30°	435.7
32.5°	337.6
35°	238.4
37.5°	150.9
40°	89.8
42.5°	56.4
45°	38.2
47.5°	24.7
50°	13.5
52.5°	6.5
55°	4.7
57.5°	4.1
60°	3.5
62.5°	3.5
65°	2.9
67.5°	2.3
70°	2.3
72.5°	1.8
75°	1.8
77.5°	1.2
80°	1.2
82.5°	0.6
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)