

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284062

Luminaire Tested: P3AS09R65B2750DE010 E3DL1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65B2750DE010 E3DL1LI_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 587.0 lumens
Efficiency: N/A
Efficacy: 44.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284062

CATALOG NUMBER: P3AS09R65B2750DE010 E3DL1LI_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1284062

CATALOG NUMBER: P3AS09R65B2750DE010 E3DL1LI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	67	64	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64	59	56	55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60	56	53	51
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138432
5°	136782
10°	131572
15°	123270
20°	110866
25°	94143
30°	73632
35°	52468
40°	34321
45°	21243
50°	10780
55°	3785
60°	3333
65°	3321
70°	3013
75°	2965
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21243 cd/sqm

TEST NUMBER: P1284062

CATALOG NUMBER: P3AS09R65B2750DE010 E3DL1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.3	9.9
10°-20°	151.1	25.7
20°-30°	176.6	30.1
30°-40°	123.4	21.0
40°-50°	54.3	9.3
50°-60°	12.1	2.1
60°-70°	6.1	1.0
70°-80°	3.7	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	386.1	65.8
0°-40°	509.5	86.8
0°-60°	575.9	98.1
0°-90°	587.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	631	
5°	621	58
15°	543	151
25°	389	177
35°	196	123
45°	68	54
55°	10	12
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1284062

CATALOG NUMBER: P3AS09R65B2750DE010 E3DL1LI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	631.3
2.5°	629.0
5°	621.4
7.5°	608.5
10°	590.9
12.5°	569.3
15°	543.0
17.5°	510.8
20°	475.1
22.5°	434.7
25°	389.1
27.5°	341.1
30°	290.8
32.5°	242.2
35°	196.0
37.5°	155.6
40°	119.9
42.5°	90.7
45°	68.5
47.5°	50.3
50°	31.6
52.5°	16.4
55°	9.9
57.5°	8.8
60°	7.6
62.5°	7.0
65°	6.4
67.5°	5.3
70°	4.7
72.5°	4.1
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)