

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285073

Luminaire Tested: P3AS13R40B2750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40B2750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 432.0 lumens
Efficiency: N/A
Efficacy: 22.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285073

CATALOG NUMBER: P3AS13R40B2750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285073

CATALOG NUMBER: P3AS13R40B2750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98	97	96	94
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	92	91	89
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90	88	86	84
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86	84	81	80
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83	80	77	76
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79	76	73	72
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73	69	67	65
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70	66	64	63
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67	64	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191147
5°	185604
10°	168423
15°	139138
20°	100365
25°	62084
30°	33600
35°	17373
40°	9446
45°	5303
50°	2661
55°	1988
60°	1798
65°	1712
70°	1667
75°	1610
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5303 cd/sqm

TEST NUMBER: P1285073

CATALOG NUMBER: P3AS13R40B2750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.7	18.0
10°-20°	166.9	38.6
20°-30°	119.1	27.6
30°-40°	43.9	10.2
40°-50°	13.8	3.2
50°-60°	4.8	1.1
60°-70°	3.3	0.8
70°-80°	2.0	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.7	84.2
0°-40°	407.6	94.3
0°-60°	426.2	98.7
0°-90°	432.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	432.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	872	
5°	843	78
15°	613	167
25°	257	119
35°	65	44
45°	17	14
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1285073

CATALOG NUMBER: P3AS13R40B2750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	871.7
2.5°	865.1
5°	843.2
7.5°	806.9
10°	756.4
12.5°	692.3
15°	612.9
17.5°	523.9
20°	430.1
22.5°	337.8
25°	256.6
27.5°	188.4
30°	132.7
32.5°	93.1
35°	64.9
37.5°	46.0
40°	33.0
42.5°	23.7
45°	17.1
47.5°	11.5
50°	7.8
52.5°	5.6
55°	5.2
57.5°	4.8
60°	4.1
62.5°	3.7
65°	3.3
67.5°	3.0
70°	2.6
72.5°	2.2
75°	1.9
77.5°	1.5
80°	1.1
82.5°	0.7
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)